


**Enclosed & Gasketed**

Listed - File E27731

Certified - File LR11851

**INTRODUCTION AND ORDERING INFORMATION**
**V Series  
Enclosed &  
Gasketed**
**Applications**

Locations requiring durable, protected lighting fixtures

Wet and dirt laden locations

Industrial environments requiring enclosed and gasketed (vapor tight) fixtures

Fixtures intended for base-up mounting

Heat resistant glass globes recommended for wet locations

**Features**

- Electrostatically applied epoxy/polyester finish
- Modular design
- Hubs are threaded for attachment to conduit
- Set screws in pendant fixtures
- Copper-free aluminum (less than 4/10 of 1%)

**Class I, Div. 2, NEMA 4 models available - see VXFC Series lighting assemblies & components, pages L9-L12. Dimensions page L13.**



| PENDANT MOUNT WITH VGA SPLICE BOX |           |          |                  |                          |              |              |              |                     |
|-----------------------------------|-----------|----------|------------------|--------------------------|--------------|--------------|--------------|---------------------|
| FIXTURE TYPE                      | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF  |              |              |                     |
|                                   |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | MOUNTING BOX | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                               | 150       | 1/2"     | VUAG-1-100 ①     | VUAGG-1-100 ①            | VGA-1        | VFC-100      | VCG-100      | VAG-100             |
|                                   |           | 3/4"     | VUAG-2-100 ①     | VUAGG-2-100 ①            | VGA-2        | VFC-100      | VCG-100      | VAG-100             |
| 200                               | 300       | 1/2"     | VUAG-1-200 ①     | VUAGG-1-200 ①            | VGA-1        | VFC-200      | VCG-200      | VAG-200             |
|                                   |           | 3/4"     | VUAG-2-200 ①     | VUAGG-2-200 ①            | VGA-2        | VFC-200      | VCG-200      | VAG-200             |



| CEILING MOUNT WITH FEET USING VBC SPLICE BOX AND VBA ADAPTER |           |          |                  |                          |                      |              |              |                     |
|--------------------------------------------------------------|-----------|----------|------------------|--------------------------|----------------------|--------------|--------------|---------------------|
| FIXTURE TYPE                                                 | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF          |              |              |                     |
|                                                              |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | MOUNTING BOX/ADAPTER | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                                                          | 150       | 1/2"     | VUXBG-1-100 ①    | VUXGG-1-100 ①            | VBC-1 + VBA          | VFC-100      | VCG-100      | VAG-100             |
|                                                              |           | 3/4"     | VUXBG-2-100 ①    | VUXGG-2-100 ①            | VBC-2 + VBA          | VFC-100      | VCG-100      | VAG-100             |
| 200                                                          | 300       | 1/2"     | VUXBG-1-200 ①    | VUXGG-1-200 ①            | VBC-1 + VBA          | VFC-200      | VCG-200      | VAG-200             |
|                                                              |           | 3/4"     | VUXBG-2-200 ①    | VUXGG-2-200 ①            | VBC-2 + VBA          | VFC-200      | VCG-200      | VAG-200             |



| CEILING MOUNT WITH VGX SPLICE BOX |           |          |                  |                          |              |              |              |                     |
|-----------------------------------|-----------|----------|------------------|--------------------------|--------------|--------------|--------------|---------------------|
| FIXTURE TYPE                      | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF  |              |              |                     |
|                                   |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | MOUNTING BOX | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                               | 150       | 1/2"     | VUXG-1-100 ①     | VUXGG-1-100 ①            | VGX-1        | VFC-100      | VCG-100      | VAG-100             |
|                                   |           | 3/4"     | VUXG-2-100 ①     | VUXGG-2-100 ①            | VGX-2        | VFC-100      | VCG-100      | VAG-100             |
| 200                               | 300       | 1/2"     | VUXG-1-200 ①     | VUXGG-1-200 ①            | VGX-1        | VFC-200      | VCG-200      | VAG-200             |
|                                   |           | 3/4"     | VUXG-2-200 ①     | VUXGG-2-200 ①            | VGX-2        | VFC-200      | VCG-200      | VAG-200             |



| CEILING MOUNT WITH VGC SPLICE BOX - FEED THROUGH |           |          |                  |                          |              |              |              |                     |
|--------------------------------------------------|-----------|----------|------------------|--------------------------|--------------|--------------|--------------|---------------------|
| FIXTURE TYPE                                     | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF  |              |              |                     |
|                                                  |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | MOUNTING BOX | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                                              | 150       | 1/2"     | VUCG-1-100 ①     | VUCGG-1-100 ①            | VGC-1        | VFC-100      | VCG-100      | VAG-100             |
|                                                  |           | 3/4"     | VUCG-2-100 ①     | VUCGG-2-100 ①            | VGC-2        | VFC-100      | VCG-100      | VAG-100             |
| 200                                              | 300       | 1/2"     | VUCG-1-200 ①     | VUCGG-1-200 ①            | VGC-1        | VFC-200      | VCG-200      | VAG-200             |
|                                                  |           | 3/4"     | VUCG-2-200 ①     | VUCGG-2-200 ①            | VGC-2        | VFC-200      | VCG-200      | VAG-200             |

\*For other colors, order globes and fixture components separately.

① Fixture supplied as component unit pack when ordered by this catalog number.

② Catalog number for ordering convenience; fixture is shipped as components as listed in catalog number table.


**KILLARK®**

**V SERIES • WEATHERPROOF  
INCANDESCENT COPPER-FREE ALUMINUM FIXTURES**



**Enclosed & Gasketed**

Listed - File E27731

Certified - File LR11851

**ORDERING INFORMATION**



| CEILING MOUNT WITH VGH SPLICE BOX - DEAD END |           |          |                  |                          |              |              |              |                     |
|----------------------------------------------|-----------|----------|------------------|--------------------------|--------------|--------------|--------------|---------------------|
| FIXTURE TYPE                                 | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF  |              |              |                     |
|                                              |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | MOUNTING BOX | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                                          | 150       | 1/2"     | VUHG-1-100 ②     | VUHGG-1-100 ②            | VGH-1        | VFC-100      | VCG-100      | VAG-100             |
|                                              |           | 3/4"     | VUHG-2-100 ②     | VUHGG-2-100 ②            | VGH-2        | VFC-100      | VCG-100      | VAG-100             |
| 200                                          | 300       | 1/2"     | VUHG-1-200 ②     | VUHGG-1-200 ②            | VGH-1        | VFC-200      | VCG-200      | VAG-200             |
|                                              |           | 3/4"     | VUHG-2-200 ②     | VUHGG-2-200 ②            | VGH-2        | VFC-200      | VCG-200      | VAG-200             |



| CEILING MOUNT WITH VXA DEEP 5-HUB SPLICE BOX |           |          |                  |                          |              |              |              |                     |
|----------------------------------------------|-----------|----------|------------------|--------------------------|--------------|--------------|--------------|---------------------|
| FIXTURE TYPE                                 | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF  |              |              |                     |
|                                              |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | MOUNTING BOX | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                                          | 150       | 1/2"     | VXAG-110 ②       | VXAGG-110 ①              | VXA-1        | VFC-100      | VCG-100      | VAG-100             |
|                                              |           | 3/4"     | VXAG-210 ②       | VXAGG-210 ②              | VXA-2        | VFC-100      | VCG-100      | VAG-100             |
| 200                                          | 300       | 1/2"     | VXAG-120 ②       | VXAGG-120 ②              | VXA-1        | VFC-200      | VCG-200      | VAG-200             |
|                                              |           | 3/4"     | VXAG-220 ②       | VXAGG-220 ②              | VXA-2        | VFC-200      | VCG-200      | VAG-200             |



| CEILING MOUNT WITH VBA ADAPTER FOR ROUND OUTLET BOX |           |          |                  |                          |             |              |              |                     |
|-----------------------------------------------------|-----------|----------|------------------|--------------------------|-------------|--------------|--------------|---------------------|
| FIXTURE TYPE                                        | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF |              |              |                     |
|                                                     |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | BOX ADAPTER | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                                                 | 150       | 1/2"     | VOB-100 ①        | VOBG-100 ①               | VBA         | VFC-100      | VCG-100      | VAG-100             |
| 200                                                 | 300       | 3/4"     | VOB-200 ②        | VOBG-200 ①               | VBA         | VFC-200      | VCG-200      | VAG-200             |

NOTES: Mounts directly to VJ ,VB or steel 3-1/2" or 4" outlet boxes. Supplied with gasket.



| CEILING MOUNT WITH VFPS ADAPTER FOR SQUARE OR OCTAGON OUTLET BOX |           |          |                  |                          |             |              |              |                     |
|------------------------------------------------------------------|-----------|----------|------------------|--------------------------|-------------|--------------|--------------|---------------------|
| FIXTURE TYPE                                                     | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF |              |              |                     |
|                                                                  |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | BOX ADAPTER | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                                                              | 150       | 1/2"     | VFCA-100 ①       | VFCA-100 ②               | VFPS        | VFC-100      | VCG-100      | VAG-100             |
| 200                                                              | 300       | 3/4"     | VFCA-200 ②       | VFCA-200 ②               | VFPS        | VFC-200      | VCG-200      | VAG-200             |

NOTES: Mounts directly to steel 4" square and 3-1/2" or 4" octagon outlet box. Supplied with gasket.


\*For other colors, order globe and fixture components separately.

① Fixture supplied as component unit pack when ordered by this catalog number.


② Catalog number for ordering convenience; fixture is shipped as components as listed in catalog number table.




**KILLARK®**




**V Fixture  
w/o Splice Box**




**V Fixture  
Globes**




**VXA**




**VGA**




**VGC VGX**




**VBC-1 & VBC-2**




**VGH**



**VB**



**VFL**



**V Stanchion**

