


**Enclosed & Gasketed**

Listed - File E27731

Certified - File LR11851

**ORDERING INFORMATION**


| PENDANT MOUNT WITH VGA SPLICE BOX |           |          |                  |                          |              |              |              |                     |
|-----------------------------------|-----------|----------|------------------|--------------------------|--------------|--------------|--------------|---------------------|
| FIXTURE TYPE                      | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF  |              |              |                     |
|                                   |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | MOUNTING BOX | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                               | 150       | 1/2"     | VUAG-1-100 ②     | VUAGG-1-100 ①            | VGA-1        | VFC-100      | VCG-100      | VAG-100             |
|                                   |           | 3/4"     | VUAG-2-100 ②     | VUAGG-2-100 ①            | VGA-2        | VFC-100      | VCG-100      | VAG-100             |
| 200                               | 300       | 1/2"     | VUAG-1-200 ②     | VUAGG-1-200 ②            | VGA-1        | VFC-200      | VCG-200      | VAG-200             |
|                                   |           | 3/4"     | VUAG-2-200 ②     | VUAGG-2-200 ②            | VGA-2        | VFC-200      | VCG-200      | VAG-200             |



| CEILING MOUNT WITH FEET USING VBC SPLICE BOX AND VBA ADAPTER |           |          |                  |                          |                      |              |              |                     |
|--------------------------------------------------------------|-----------|----------|------------------|--------------------------|----------------------|--------------|--------------|---------------------|
| FIXTURE TYPE                                                 | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF          |              |              |                     |
|                                                              |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | MOUNTING BOX/ADAPTER | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                                                          | 150       | 1/2"     | VUXBG-1-100 ①    | VUXBGG-1-100 ①           | VBC-1 + VBA          | VFC-100      | VCG-100      | VAG-100             |
|                                                              |           | 3/4"     | VUXBG-2-100 ①    | VUXBGG-2-100 ①           | VBC-2 + VBA          | VFC-100      | VCG-100      | VAG-100             |
| 200                                                          | 300       | 1/2"     | VUXBG-1-200 ②    | VUXBGG-1-200 ②           | VBC-1 + VBA          | VFC-200      | VCG-200      | VAG-200             |
|                                                              |           | 3/4"     | VUXBG-2-200 ②    | VUXBGG-2-200 ②           | VBC-2 + VBA          | VFC-200      | VCG-200      | VAG-200             |



| CEILING MOUNT WITH VGX SPLICE BOX |           |          |                  |                          |              |              |              |                     |
|-----------------------------------|-----------|----------|------------------|--------------------------|--------------|--------------|--------------|---------------------|
| FIXTURE TYPE                      | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF  |              |              |                     |
|                                   |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | MOUNTING BOX | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                               | 150       | 1/2"     | VUXG-1-100 ②     | VUXGG-1-100 ②            | VGX-1        | VFC-100      | VCG-100      | VAG-100             |
|                                   |           | 3/4"     | VUXG-2-100 ②     | VUXGG-2-100 ②            | VGX-2        | VFC-100      | VCG-100      | VAG-100             |
| 200                               | 300       | 1/2"     | VUXG-1-200 ②     | VUXGG-1-200 ②            | VGX-1        | VFC-200      | VCG-200      | VAG-200             |
|                                   |           | 3/4"     | VUXG-2-200 ②     | VUXGG-2-200 ②            | VGX-2        | VFC-200      | VCG-200      | VAG-200             |



| CEILING MOUNT WITH VGC SPLICE BOX - FEED THROUGH |           |          |                  |                          |              |              |              |                     |
|--------------------------------------------------|-----------|----------|------------------|--------------------------|--------------|--------------|--------------|---------------------|
| FIXTURE TYPE                                     | LAMP WATT | HUB SIZE | CATALOG NUMBER   |                          | CONSISTS OF  |              |              |                     |
|                                                  |           |          | FIXTURE W/ GLOBE | FIXTURE W/ GLOBE & GUARD | MOUNTING BOX | FIXTURE BODY | CLEAR GLOBE* | GUARD (if selected) |
| 100                                              | 150       | 1/2"     | VUCG-1-100 ②     | VUCGG-1-100 ①            | VGC-1        | VFC-100      | VCG-100      | VAG-100             |
|                                                  |           | 3/4"     | VUCG-2-100 ②     | VUCGG-2-100 ②            | VGC-2        | VFC-100      | VCG-100      | VAG-100             |
| 200                                              | 300       | 1/2"     | VUCG-1-200 ②     | VUCGG-1-200 ②            | VGC-1        | VFC-200      | VCG-200      | VAG-200             |
|                                                  |           | 3/4"     | VUCG-2-200 ②     | VUCGG-2-200 ②            | VGC-2        | VFC-200      | VCG-200      | VAG-200             |

\*For other colors, order globes and fixture components separately.

① Fixture supplied as component unit pack when ordered by this catalog number.

② Catalog number for ordering convenience; fixture is shipped as components as listed in catalog number table.


**KILLARK®**



**Pendant**



**Ceiling**

**Enclosed & Gasketed\***



Listed - File E10514



Certified - File LR11713

**FEATURES-SPECIFICATIONS**

**V SERIES  
ENCLOSED & GASKETED  
Applications**

Locations requiring durable, protected lighting fixtures  
Wet and dirt laden locations, such as industrial environments requiring enclosed and gasketed (vapor-tight) fixtures  
Lighting walkways, tunnels, loading docks, exits, stairwells, etc  
Fixtures intended for base-up mounting  
Heat resistant glass globes recommended for wet locations


**Features**

- Electrostatically applied epoxy/polyester finish
- Enclosed and gasketed fixture (vapor-tight). Joint gaskets provided to seal out moisture and dirt
- Splice box selections include pendant, ceiling, bracket and stanchion mounting types
- Modular design permits selection of splice box, fixture body, globe, guard and reflector for specific or custom applications
- Hubs are threaded for attachment to conduit and set screws are provided in pendant fixtures
- Copper-free aluminum (less than 4/10 of 1%) construction with electrostatically applied epoxy/polyester finish resists corrosion


**\*Class I, Div. 2, NEMA 4 models available - see VXFC Series lighting assemblies & components, pages L9-L12. Dimensions page L13.**




**KILLARK®**




**V Fixture  
w/o Splice Box**




**V Fixture  
Globes**





**VXA**




**VGA**




**VGC VGX**




**VBC-1 & VBC-2**




**VGH**



**VB**



**VFL**



**V Stanchion**

