



STANCHION 25°



STANCHION STRAIGHT



EZ ADAPTER

ORDERING INFORMATION

VM1L SERIES 25° STANCHION WITH OPTIC AND GUARD ①							
WATTS	HUB SIZE②	VOLTAGE③	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	8" SPIN-TOP TYPE V REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
45	1-1/2"	120-277VAC	VM1L4530D5GLG	VM1L4530D5R1G	VM1L4530D5R5G	VM1L4530D5S8G	VM1L4530D5S5G

VM1L SERIES STRAIGHT STANCHION WITH OPTIC AND GUARD ①							
WATTS	HUB SIZE②	VOLTAGE③	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	8" SPIN-TOP TYPE V REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
45	1-1/2"	120-277VAC	VM1L4530S5GLG	VM1L4530S5R1G	VM1L4530S5R5G	VM1L4530S5S8G	VM1L4530S5S5G

VM1L SERIES EZ ADAPTER WITH OPTIC AND GUARD ①							
WATTS	HUB SIZE④	VOLTAGE③	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	8" SPIN-TOP TYPE V REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
45	④	120-277VAC	VM1L4530EZGLG	VM1L4530EZR1G	VM1L4530EZR5G	VM1L4530EZS8G	VM1L4530EZS5G

- ① Catalog numbers shown are with Guard; to omit guard change ending G to N; e.g. VM1L4530D5GLN
- ② Catalog numbers shown are with 1-1/2" conduit openings; change "5" to "4" for 1-1/4" e.g. VM1L4530D4GLG
- ③ 120VAC through 277VAC 50/60Hz
- ④ VMEZA tank adapters UL "classified" as an assembly for use between VM tanks and EZ mounts. Order EZ mounts separately (see below).



Pendant

Ceiling

Wall Bracket

25° Stanchion

MOUNTING BOXES FOR EZ ADAPTER				
CATALOG NUMBER				HUB SIZE
PENDANT	CEILING	BRACKET	STANCHION	
EZA2	EZX2	EZB2	—	3/4"
EZA3	EZX3	EZB3	—	1"
—	—	—	EZD4*	1-1/4"/1-1/2**

*1-1/2" furnished with 1-1/2"-1-1/4" reducer and extension.