



FXCS-0K2A522A - FXCS Series, AL
Maintained Contact 2-Position Keyed
Selector Switch Cvr w/ Device, Key
Removal in Left, Off-On Blank, 2 NO/2NC
Contact

By Killark
Catalog # FXCS-0K2A522A

FXCS SERIES - ALUMINUM MAINTAINED CONTACT 2-POSITION
KEYED SELECTORSWITCH COVER WITH DEVICE - FACTORY
SEALED - KEYED ALIKE WITH KEY REMOVALIN LEFT POSITION
- "OFF-ON"/BLANK NAMEPLATE - 2NO/2NC CONTACT

Features

- Eliminates external sealing requirements.
- Lower installation cost.
- NEMA 3 weatherproof.
- Color coded wiring with more wiring space for easier field installation.
- Stainless steel captive screws for cover assembly.
- Lockout accessory available must be factory installed.
- Ground boss for grounding in the splice box.
- Device bodies and covers are copper-free cast aluminum alloy.
- Push button, selector switches and pilot light bodies are copper-free aluminum.
- Operating shaft in both push buttons and selector switches are stainless steel.

Application

SEAL-X Series is used to prevent the igniting of external hazardous atmospheres by the enclosed arcing devices in such areas as: hazardous locations due to the presence of flammable gases or vapors, combustible dusts or easily ignitable fibers or flyings

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3
UL File Number	E53360, E12379
CSA File Number	LR11714, LR11712
Buy America(n) Qualified	Contact Manufacturer

Conductor

Number Of Poles	1
-----------------	---

Configuration



Back Box Type	FXB
Current	
Contact Rating	• 60A INRUSH @ 120 VAC • 30A INRUSH @ 240 VAC • 15A INRUSH @ 480 VAC • 12A INRUSH @ 600 VAC • 6A BREAKING @ 120 VAC • 3A BREAKING @ 240 VAC • 1.5A BREAKING @ 480 VAC • 1.2A BREAKING @ 600 VAC • 10A CARRYING @ 120 VAC • 10A CARRYING @ 240 VAC • 10A CARRYING @ 480 VAC
Amperage Rating	10 A
Frequency Rating	50/60 Hz
Dimensions	
Gross Weight with Packaging	3.14
Width	6 in
Weight	3.14 lb.
Height	4.38 in
Length	6.63 in
Dimensions	6.63 in x 6 in x 4.38 in
General	
Type	Aluminum Factory Sealed Cover With 2-Position Key Selector Switch
Series	FXCS Series
Material	Copper-free aluminum
UPC	783936016979
Color	Black
Logistics	
Factory Sealed	Factory Sealed
Operational	
Action	Maintained
Actuator	2 Position Key Selector Switch

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)

[Installation Manual \[French\]](#)



A Hubbell brand