



FXCS-2B4 - FXCS Series, AL Dead-End Momentary Contact Double Push Button Control Station, Red/Green Buttons w/ Start Nameplates, Hub Size 3/4", 1NO/1NC

By Killark
Catalog # FXCS-2B4

FXCS Series - Aluminum Dead-End Momentary Contact Double Push Button Control Station - Factory Sealed - Red And Green Buttons With "Start" Nameplates - Hub Size 3/4 Inch - 1NO/1NC Contact Rating

Features

- Eliminates external sealing requirements.
- Lower installation cost.
- NEMA 3 weatherproof.
- Color coded wiring with more wiring space for easier field installation.
- Stainless steel captive screws for cover assembly.
- Lockout accessory available must be factory installed.
- Ground boss for grounding in the splice box.
- Device bodies and covers are copper-free cast aluminum alloy.
- Push button, selector switches and pilot light bodies are copper-free aluminum.
- Operating shaft in both push buttons and selector switches are stainless steel.

Application

SEAL-X Series is used to prevent the igniting of external hazardous atmospheres by the enclosed arcing devices in such areas as: hazardous locations due to the presence of flammable gases or vapors, combustible dusts or easily ignitable fibers or flyings

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR11714, LR11712
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
Nema Rating	3
UL File Number	E53360, E12379
Buy America(n) Qualified	Contact Manufacturer

Conductor

Number Of Poles	2
-----------------	---

Configuration

Back Box Type	FXB
---------------	-----



Hub Pattern	Dead-End
Current	
Amperage Rating	10 A
Frequency Rating	50/60 Hz
Contact Rating	• 60A INRUSH @ 120 VAC • 30A INRUSH @ 240 VAC • 15A INRUSH @ 480 VAC • 12A INRUSH @ 600 VAC • 6A BREAKING @ 120 VAC • 3A BREAKING @ 240 VAC • 1.5A BREAKING @ 480 VAC • 1.2A BREAKING @ 600 VAC • 10A CARRYING @ 120 VAC • 10A CARRYING @ 240 VAC • 10A CARRYING @ 480 VAC
Dimensions	
Depth	5.06 in
Hub Size	3/4"
Length	6.63 in
Gross Weight with Packaging	4.4
Width	6 in
Height	4.38 in
Dimensions	6.63 in x 6 in x 4.38 in
General	
Series	FXCS Series
Color	Green-Red
Type	Factory Sealed
UPC	783936201177
Logistics	
Factory Sealed	Factory Sealed
Operational	
Action	Momentary
Actuator	Single Pushbutton

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)

[Installation Manual \[French\]](#)



A Hubbell brand