

Key Operated
Selector Switch

Class I, Div. 1 & 2, Groups B,C,D®
Class 1, Zones 1 & 2, Groups IIB, IIA
Class II, Div. 1 & 2, Groups E,F,G
Class III
NEMA 3, 4, 4X, 7(B,C,D) 9(E,F,G)

See Area Classification Chart
page C40 for Details



Listed - File E12379



Certified - File LR11714

See files for details or call Killark.

FEATURES-SPECIFICATIONS

G KEY SELECTOR SWITCH MAINTAINED CONTACT ④				
CATALOG NUMBER ①			CONTACT ARRANGEMENT ③	TYPE OF OPERATION ②⑤
SHORT ⑥	LONG	EXTENDED		
G028-2A3F22D	G08-2A3F22D N34	G0L82A322D	Left Right	Two position
G028-3C3G32D	G08-3C3G32D N34	G0L83C332D	Left Center Right	Three position

G KEY SELECTOR SWITCH MAINTAINED CONTACT WITHOUT CONTACTS ④				
G028-2A0F22D	G08-2A0F22D N34	G0L82A022D	None	Two position
G028-3C0G32D	G08-3C0G32D N34	G0L83C032D	None	Three position

G KEY SELECTOR SWITCH SPRING RETURN ④				
G056-2L3F22D	G036-2L3F22D N34	G0L36L322D	Left Right	Two position spring return to left
G057-3C6G32D	G037-3C6G32D N34	G0L37C632D	Left Center Right	Three position spring return to center from right or left
G058-3L6G32D	G038-3L6G32D N34	G0L38L632D	Left Center Right	Three position spring return to center from right, maintain in left
G059-3R6G32D	G039-3R6G32D N34	G0L39R632D	Left Center Right	Three position spring return to center from left, maintain in right

G KEY SELECTOR SWITCH SPRING RETURN WITHOUT CONTACTS ④				
G056-2L0F22D	G036-2L0F22D N34	G0L36L022D	None	Two position spring return to left
G057-3C0G32D	G037-3C0G32D N34	G0L37C032D	None	Three position spring return to center from right or left
G058-3L0G32D	G038-3L0G32D N34	G0L38L032D	None	Three position spring return to center from right, maintain in left
G059-3R0G32D	G039-3R0G32D N34	G0L39R032D	None	Three position spring return to center from left, maintain in right

①Refer to catalog page C30 to select proper operator for enclosure, pages C38 & C39 for Accessories, page C30 for complete details on Area Classification of operators, page C42 for Dimensional Information, page C40 for Special Contact Configurations.

②Nameplates are Double sided. 2 position marked ON-OFF and Blank on other side. 3 position marked HAND-OFF-AUTO and Blank on other side. 4 position is Blank.

③Contact Blocks are shown in their normal position.

④All Key Operators are furnished Keyed Different If Keyed Alike is required substitute letter "A" for letter "D" in catalog number.

⑤Keys are removable in Left position on 2 position selectors and in Center position on 3 position selectors. For key removal in ALL positions change "22" in 2 position to "20" and "32" in 3 position to "30".

⑥Short style operators are suitable for Class I Group C & D, Class II Group E,F,G only.



KILLARK®