



MBL SERIES

KILLARK

COMPACT SIZE – COMPONENTS



MB MOUNTING BRACKETS				
CATALOG NUMBER				HUB SIZE
PENDANT	CEILING	WALL	STANCHION	
MBA-2	MBX-2	MBB-2	—	3/4"
MBA-3	MBX-3	MBB-3	—	1"
—	MBX-8*	—	—	M20
—	—	—	MBD-4	1-1/4"
—	—	—	MBD-5	1-1/2"

* MBX-8 furnished with 3 non-metallic plugs



**Non-Glass Polycarbonate
8" Flat Lens or Spin-top**




MBL LED OPTICS AND ACCESSORIES		
DESCRIPTION	OPTIC LOGIC	GUARD
Globe (glass)	MBG (GL)	MBAG
Reflector (all glass) Type V	VMR175 (R5)	VMAG17
Reflector (spin top) 8" Type V	VZRG1550 (S8)	VMRWG8
Reflector (spin top) 12" Type V	VZRG2550 (S5)	VMRWGS
8" Spin-top flat lens (glass)	VZRGF8 (GF)	VZRF8GRD
8" Spin-top flat lens (polycarbonate)	VZRPF8 (PF)	VZRF8GRD
Reflector polycarbonate (spin -top) 12" Type V	VZRP175 (P5)	VMRWGS
Pathway Reflector	VZRF8PR	NA
Reflector for MBG Globe - DOME	VMPSD-17	NA
Reflector for MBG Globe - ANGLE	VMPA-17	NA
120VAC Photocell with FS Style Cover	VMFSPC1	NA
208-277VAC Photocell with FS Style Cover	VMFSPC2	NA
3-sided EXIT Accessory (use without guard)	VEXA100B	NA

14-25W only


Reflectors for use with MBG/MBAG only; VMG17 globe with VMAG17 guard will fit without reflector.




COMPACT SIZE – DIMENSIONS & WEIGHTS




MBL Flat Lens, Pathway Reflector Wall Mount




MBA Pendant




MBB Wall Mount




MBX Ceiling




MBD Stanchion




MBL Tank with Flat Lens




MBL Pendant, Globe, Guard




MBL & MBG Globe Only




MBL & 8" Type V Spin-top




MBL Flat Lens Ceiling Mount



MBL Pendant, Refractor, Guard



MBL & VMR Refractor



MBL & 12" Type V Spin-top

TYPICAL WEIGHTS (LBS.) W/STANDARD GLOBE AND GUARD - MBL SERIES

14-25W	Pendant 14.96	Ceiling 15.96	Wall 19.30	Stanchion 16.83
40-50W	Pendant 20.96	Ceiling 21.69	Wall 25.30	Stanchion 22.83



ACCESSORIES/DIMENSIONS

Globe



MBG

Refractor



VZRG1550

Guards



MBAG



VMRWG8

Reflectors



VMPD17



VMPI17

ORDERING INFORMATION

MB ACCESSORIES	
CATALOG NUMBER	DESCRIPTION
MBG	Heat and impact resistant globe
VZRG1550	(I.E.S. Type V) closed bottom 8 glass refractor
MBAG	Globe guard - Epoxy/polyester painted aluminum
VMRWG8	Refractor guard - plated steel
VMPD17	Standard dome reflector (fiberglass reinforced polyester)
VMPI17	Angle reflector (fiberglass reinforced polyester)

Dimensions

