



Listed - File E27731

Certified - File LR11851



V GLASS GLOBES		
CATALOG NUMBER		DESCRIPTION
150 W A-21 LAMP	300 W PS-25 LAMP	
VCG-100	VCG-200	Clear
VCGP-100	VCGP-200	Clear Tempered. Thermal and shock resistant ^①
VCGPT-100	—	Clear Tempered with Tuffskin [®] coating ^②
VAMG-100	VAMG-200	Amber
VAMGP-100	—	Amber Tempered ^①
VGG-100	VGG-200	Blue Green
VGGP-100	VGGP-200	Blue Green Tempered ^①
VBG-100	—	Blue
VBG-100	—	Blue Tempered ^①
VRG-100	VRG-200	Ruby
VRGP-100	VRGP-200	Ruby Tempered ^①
VRSG-100	—	Green
VPG-100	—	Purple
75 W A-19 LAMP	150 W A-21 LAMP	Polycarbonate. Cannot be used with guard or in high ambient temperature locations (40°C/104°F max.) Not UL Listed.
VPLCG-100	VPLCG-200	
500 W PS-35 LAMP		
VCG-500		Clear (for replacement) Formerly DCG-20
VCGP-500		Tempered. Thermal and shock resistant (for replacement).

^① Recommended for use with VXFC fixture basis.

^② TM Thomas Manufacturing.


V GUARDS	
CATALOG NUMBER	DESCRIPTION
VAG-100	100 Series Vaportite guard
VAG-200	200 Series Vaportite guard



V REFLECTORS		
CATALOG NUMBER	DESCRIPTION	
VPRSD-100	100 Series Reflector	16 3/8" Dia. 5 5/8" High. White polypropylene for pendant & ceiling applications. Not for use with wall or stanchion models.
VPRSD-200	200 Series Reflector	



Body To Splice Box
Gasket
100 or 200 Series
VTG Standard
VTG-S Silicone (pictured)

V SERIES GASKETS			
CATALOG NUMBER		TYPE	DESCRIPTION
100 SERIES	200 SERIES		
VTG		VFC	Fixture body to splice box
VTG-S		VXFC	Silicone, Fixture body to splice box
VBNB		—	Replacement Gaskets for VB-1/VB-2 and VBA
15871AABB	VTGG	VFC	Globe gasket
VTGG1-S	VTGG2-S	VFXC	Silicone, globe gasket



Globe Gasket
100 Series Standard - 15871AABB
200 Series Standard - VTGG (pictured)
100 Series Silicone - VTGG1-S
200 Series Silicone - VTGG2-S



V LAMP SOCKET	
CATALOG NUMBER	DESCRIPTION
VRME	For fixture types 100 and 200


KILLARK[®]