


## RER20-TC



**Color:** Toasted Coconut

**UPC Code:** 07847753552

**Country Of Origin:** China

**NEMA:**  
5-20R



### Brand Features

Renu in a snap! Renu is the smart new line of decorative electrical products from Leviton. Install Renu and get a fresh stylish look, plus the ability to change the color of any Renu device when you update a room. The Renu line includes switches, outlets, GFCI outlets, dimmers, and sleek, screwless wallplates available in 20 designer colors. The RER20 20A tamper-resistant outlet has built-in shutters to help prevent access by most foreign objects. Shallow in size, it is self-grounded\*, and back and side wired for fast, easy installation. The terminals are designed to withstand high torque and resist wire pullout. A Renu 15A-125V tamper-resistant outlet is also available. Use only with Renu wallplates. \*When installed in a properly grounded metal wallbox.

### Item Description

Leviton Renu® Tamper-Resistant Outlet RER20-TC, 20A-125V, in Toasted Coconut

### Technical Information

#### Product Features

**Color:** Toasted Coconut

**Color Change Kit:** RKR20

**Device Type:** Duplex Outlet

**Grounding:** Self-Grounding Clip and Green Ground Screw

**NEMA:** 5-20R

**Product Family:** Renu

**Ratings:** 20A-125V

**Standards and Certifications:** cULus

**Termination:** Back & Side

**Warranty:** 5 Year Limited

**Amperage:** 20 A

### Features and Benefits

- 20A-125V
- Tamper-resistant to meet the child safety requirements of the National Electrical Code®
- Built-in shutters help prevent access by most foreign objects
- Available in 20 popular colors to match any décor
- Once installed, Renu outlets can be updated to a new color by ordering an RKR20 color change kit
- Outlet face easily snaps OFF and ON to change color
- To complete the look, snap on a matching or contrasting Renu screwless wallplate (sold separately)
- Turns the electrical device into a decorative, easily updated accessory
- Shallow size is easy to install in any wallbox
- Self-grounded when installed in a properly grounded metal wallbox
- Back and side wired for fast, easy installation
- Terminals designed to withstand high torque and resist wire pullout
- 15A tamper-resistant outlet is also available
- Use only with Renu wallplates

**Patents\***

US8242362

USD662885

\*This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.

**SPECIFICATION SUBMITTAL**

|                                          |                                                 |                      |
|------------------------------------------|-------------------------------------------------|----------------------|
| <b>JOB NAME:</b><br><input type="text"/> | <b>CATALOG NUMBERS:</b><br><input type="text"/> |                      |
| <b>JOB NUMBER:</b> <input type="text"/>  | <input type="text"/>                            | <input type="text"/> |

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2018 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

