



Color: Wood Smoke

UPC Code: 07847753549

Country Of Origin: China

NEMA:
5-20R



RER20-WS

Brand Features

Renu in a snap! Renu is the smart new line of decorative electrical products from Leviton. Install Renu and get a fresh stylish look, plus the ability to change the color of any Renu device when you update a room. The Renu line includes switches, outlets, GFCI outlets, dimmers, and sleek, screwless wallplates available in 20 designer colors. The RER20 20A tamper-resistant outlet has built-in shutters to help prevent access by most foreign objects. Shallow in size, it is self-grounded*, and back and side wired for fast, easy installation. The terminals are designed to withstand high torque and resist wire pullout. A Renu 15A-125V tamper-resistant outlet is also available. Use only with Renu wallplates. *When installed in a properly grounded metal wallbox.

Item Description

Leviton Renu® Tamper-Resistant Outlet RER20-WS, 20A-125V, in Wood Smoke

Technical Information

Product Features

Color: Wood Smoke

Color Change Kit: RKR20

Device Type: Duplex Outlet

Grounding: Self-Grounding Clip and Green Ground Screw

NEMA: 5-20R

Product Family: Renu

Ratings: 20A-125V

Standards and Certifications: cULus

Termination: Back & Side

Warranty: 5 Year Limited

Features and Benefits

- 20A-125V
- Tamper-resistant to meet the child safety requirements of the National Electrical Code®
- Built-in shutters help prevent access by most foreign objects
- Available in 20 popular colors to match any décor
- Once installed, Renu outlets can be updated to a new color by ordering an RKR20 color change kit
- Outlet face easily snaps OFF and ON to change color
- To complete the look, snap on a matching or contrasting Renu screwless wallplate (sold separately)
- Turns the electrical device into a decorative, easily updated accessory
- Shallow size is easy to install in any wallbox
- Self-grounded when installed in a properly grounded metal wallbox
- Back and side wired for fast, easy installation
- Terminals designed to withstand high torque and resist wire pullout
- 15A tamper-resistant outlet is also available
- Use only with Renu wallplates

Patents*

US8242362

USD662885

*This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.

SPECIFICATION SUBMITTAL

JOB NAME: 	CATALOG NUMBERS: 	
JOB NUMBER:		

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

