


Outside Micrometer with Heat Ins. Plate

Item number: 102-311

Images



Description

Cut-away frame behind anvil for measuring in hard to reach places. A ratchet stop or friction thimble guarantees repeatable measurement.


Features

Digital/Analog:	Analog
Delivered:	Including box, key, setting standard (from 25 mm upward), certificate of inspection (0-50 mm range)
Inch-Metric:	Metric
Range:	0 - 25 mm
Max. Permissible Error J MPE:	$\pm 1 \mu\text{m}$
Flatness:	$0,3 \mu\text{m}$
Parallelism:	$2 \mu\text{m}$
Remarks:	Ratched Stop
Measuring face:	Carbide-tipped, micro-lap finish
Measuring spindle:	With spindle lock, $\varnothing 6,35 \text{ mm}$, spindle pitch $0,5 \text{ mm}$
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 18 \text{ mm}$

Measuring force: 5 - 10 N

Mass: 180 g

Dimensions



L: 0 mm

a: 5 mm

b: 26 mm

c: 2.5 mm

Accessories

Optional accessories:



Color Ratchet Stop

for Analog Micrometer 0-300 mm Black
Art No. 985056
Suggested retail price: 15.00 €*



Color Ratchet Stop

for Analog Micrometer 0-300 mm Red
Art No. 985061
Suggested retail price: 15.00 €*



Micrometer Stand, 45° Angle Type

for Micrometer 0-50mm/0-2"
Art No. 156-105-10
Suggested retail price: 58.00 €*

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"
Art No. 156-101-10
Promo price: **55.90 €***
Suggested retail price: ~~70.00 €*~~

Color Ratchet Stop

for Analog Micrometer 0-300 mm Blue
Art No. 985081
Suggested retail price: 15.00 €*



Color Ratchet Stop

for Analog Micrometer 0-300 mm Yellow
Art No. 985071
Suggested retail price: 15.00 €*



Color Ratchet Stop

for Analog Micrometer 0-300 mm Green
Art No. 985076
Suggested retail price: 15.00 €*



Color Ratchet Stop

for Analog Micrometer 0-300 mm Brown
Art No. 985066
Suggested retail price: 15.00 €*



Micrometer Ratchet Stop Plastic

for Analog Micrometer 0-300 mm, Grey
Art No. 04GZA239
Suggested retail price: 12.00 €*

