


Tubular Inside Micrometer with Extension

Item number: 139-203

Images



Description

This is an extension pipe type inside micrometer that offers you the following benefits:

- Interchangeable extensions in a hollow pipe design.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	40 - 300 mm
Measuring span:	10 mm
Graduation:	0.01 mm
Spindle feed error:	6 μ m
Limit of error:	$\pm(6+\text{max. measurement length}/50)$ μ m
Scale:	Thimble and sleeve satin chrome finish, \varnothing 18 mm \varnothing 13 mm (139-203, 139-204)
Measuring spindle:	Spindle pitch 0.5 mm
Measuring face:	Carbide
Measuring method:	2-point
Extension rods:	8 (10, 20, 30, 60, 90, 110, 120, 130 mm)
Delivered:	Including box, spanner, extension rods (8 pcs.), micrometer head 139-003
Mass:	240 g

Dimensions



Accessories

Standard accessories:



Main Unit for Tubular Inside Micrometer

Carbide Tipped 100-125mm
Art No. 139-001
Suggested retail price: 251.00 €*



Tubular Inside Micrometer 100-110mm

for 139-203
Art No. 139-003
Suggested retail price: 146.00 €*



Tubular Inside Micrometer 100-125mm

for 139-204
Art No. 139-005
Suggested retail price: 152.00 €*

Spare parts

Consumable spares:



Extension Rod for Series 139, 339

25mm
Art No. 981003
Suggested retail price: 43.00 €*



Extension Rod for Series 139, 339

50mm
Art No. 981005
Suggested retail price: 49.00 €*



Extension Rod for Series 139, 339

100mm
Art No. 981007
Suggested retail price: 93.00 €*



Extension Rod for Series 139, 339

200mm
Art No. 981009
Suggested retail price: 109.00 €*



Extension Rod for Series 139, 339

400mm
Art No. 981011
Suggested retail price: 125.00 €*



Extension Rod 10mm

for 139-203
Art No. 981981
Price on application

Extension Rod 20mm

for 139-203

Art No. 981982

Price on application



Extension Rod 30mm

for 139-203

Art No. 981983

Price on application



Extension Rod 60mm

for 139-203

Art No. 981984

Price on application



Extension Rod 90mm

for 139-203

Art No. 981985

Price on application



Extension Rod 110mm

for 139-203

Art No. 981986

Price on application



Extension Rod 120mm

for 139-203

Art No. 981987

Price on application



Extension Rod 130mm

for 139-203

Art No. 981988

Price on application



Extension Rod 25mm

for 139-204

Art No. 981991

Price on application



Extension Rod 75mm

for 139-204

Art No. 981993

Price on application



Extension Rod 150mm

for 139-204

Art No. 981994

Price on application



Extension Rod 225mm

for 139-204

Art No. 981995

Price on application



Extension Rod 300mm

for 139-204

Art No. 981996

Price on application



Extension Rod 350mm

for 139-204

Art No. 981997

Price on application



Extension Rod 400mm

for 139-204

Art No. 981998

Price on application



Extension Rod 425mm

for 139-204

Art No. 981999

Price on application



Extension Rod 450mm

for 139-204

Art No. 982000

Price on application

