



PLASTIC WASHERS

17W/16FW Series (continued)
Nylon Flat Washers

Specifications:

- Material: UL94 V-2 Nylon 6/6
- Color: See Table

Features:

- Resistant to corrosion and many chemicals

| Item No. | | ID | OD | Thickness | Bulk Pack Qty |
|---------------|----------------|-------|-------|-----------|---------------|
| Natural | Black | in | in | in | |
| 17M16DIN34816 | 17M16DIN34816B | 0.669 | 1.969 | 0.130 | 1000 |
| 17W12524 | 17W12524B | 0.670 | 1.240 | 0.060 | 500 |
| 17W10035 | 17W10035B | 0.675 | 1.000 | 0.200 | 500 |
| 17W10619 | 17W10619B | 0.680 | 1.062 | 0.150 | 500 |
| 17W08651 | 17W08651B | 0.688 | 0.865 | 0.155 | 500 |
| 17W08653 | 17W08653B | 0.690 | 0.862 | 0.220 | 500 |
| 17W08805* | 17W08805B | 0.690 | 0.880 | 0.032 | 500 |
| 17W09600 | 17W09600B | 0.692 | 0.960 | 0.126 | 500 |
| 17W08121 | 17W08121B | 0.695 | 0.812 | 0.093 | 1000 |
| 17W15005 | 17W15005B | 0.696 | 1.500 | 0.120 | 500 |
| 17W17251 | 17W17251B | 0.697 | 1.425 | 0.100 | 500 |
| 17W09260 | 17W09260B | 0.705 | 0.926 | 0.124 | 500 |
| 17W08711* | 17W08711B | 0.706 | 0.871 | 0.111 | 500 |
| 17W09372* | 17W09372B | 0.710 | 0.945 | 0.060 | 1000 |
| 17W10626 | 17W10626B | 0.728 | 1.102 | 0.039 | 500 |
| 17W08400 | 17W08400B | 0.730 | 0.840 | 0.125 | 500 |
| 17W09844 | 17W09844B | 0.730 | 0.993 | 0.097 | 500 |
| 17W10007 | 17W10007B | 0.730 | 1.000 | 0.062 | 500 |
| 17W10620 | 17W10620B | 0.740 | 1.060 | 0.100 | 500 |
| 17W10622 | 17W10622B | 0.740 | 1.062 | 0.225 | 500 |
| MFW130A | — | 0.748 | 1.339 | 0.118 | 250 |
| 17W08769* | 17W08769B | 0.750 | 0.875 | 0.160 | 500 |
| 17W09907 | 17W09907B | 0.750 | 1.000 | 0.125 | 500 |
| 17W15020 | 17W15020B | 0.750 | 1.500 | 0.250 | 250 |
| 17W15050 | 17W15050B | 0.750 | 1.505 | 0.053 | 1000 |
| 17W08652 | 17W08652B | 0.755 | 0.875 | 0.125 | 500 |
| 17W07539* | 17W07539B | 0.755 | 0.962 | 0.101 | 500 |
| 17W10017 | 17W10017B | 0.755 | 1.000 | 0.175 | 500 |
| 17W14252 | 17W14252B | 0.755 | 1.485 | 0.197 | 500 |
| 17W15004 | 17W15004B | 0.755 | 1.500 | 0.130 | 500 |
| 17W09901 | 17W09901B | 0.760 | 1.000 | 0.062 | 500 |
| 17W09905* | 17W09905B | 0.760 | 1.000 | 0.281 | 500 |
| 17W14250 | 17W14250B | 0.760 | 1.420 | 0.100 | 1000 |
| 17W11258 | 17W11258B | 0.763 | 1.125 | 0.125 | 1000 |
| 17W12503 | 17W12503B | 0.765 | 1.250 | 0.080 | 1000 |
| 17W13102 | 17W13102B | 0.765 | 1.312 | 0.063 | 1000 |
| 17W17252 | 17W17252B | 0.765 | 1.490 | 0.100 | 500 |
| 17W09930 | 17W09930B | 0.771 | 0.993 | 0.124 | 500 |
| 17W08770* | 17W08770B | 0.780 | 0.891 | 0.505 | 500 |
| 17W09853 | 17W09853B | 0.781 | 1.000 | 0.075 | 500 |
| 17W13747 | 17W13747B | 0.781 | 1.375 | 0.063 | 500 |
| 17W15054 | 17W15054B | 0.790 | 1.500 | 0.120 | 500 |
| 17W15053 | 17W15053B | 0.795 | 1.575 | 0.039 | 1000 |
| 17W08710* | 17W08710B | 0.797 | 0.887 | 0.500 | 500 |
| 17W12252* | 17W12252B | 0.799 | 1.201 | 0.118 | 500 |
| 17W25002 | 17W25002B | 0.800 | 2.500 | 0.063 | 250 |
| 17W14611 | 17W14611B | 0.802 | 1.455 | 0.125 | 500 |
| 17W12507 | 17W12507B | 0.805 | 1.250 | 0.060 | 500 |
| 17W20062 | 17W20062B | 0.805 | 2.000 | 0.062 | 250 |
| 17W30062 | 17W30062B | 0.805 | 2.969 | 0.062 | 250 |
| 17W15051 | 17W15051B | 0.810 | 1.490 | 0.062 | 1000 |
| 17W10570 | 17W10570B | 0.812 | 1.057 | 0.125 | 1000 |
| 17W12510 | 17W12510B | 0.812 | 1.250 | 0.080 | 1000 |
| 17W17242 | 17W17242B | 0.812 | 1.750 | 0.125 | 500 |
| 17W31250 | 17W31250B | 0.812 | 3.132 | 0.125 | 250 |
| 17W11005* | 17W11005B | 0.827 | 1.181 | 0.157 | 500 |
| 17M20DIN34815 | 17M20DIN34815B | 0.827 | 1.457 | 0.118 | 250 |
| 17W12517 | 17W12517B | 0.839 | 1.250 | 0.040 | 1000 |
| 17W11140* | 17W11140B | 0.840 | 1.114 | 0.127 | 500 |
| 17W10571 | 17W10571B | 0.844 | 1.000 | 0.125 | 500 |
| 17W10311 | 17W10311B | 0.844 | 1.031 | 0.040 | 1000 |
| 17W10623 | 17W10623B | 0.855 | 1.107 | 0.058 | 500 |
| 17W11002 | 17W11002B | 0.875 | 1.117 | 0.195 | 500 |
| 17W12502 | 17W12502B | 0.875 | 1.250 | 0.125 | 1000 |
| 17W12032 | 17W12032B | 0.880 | 1.280 | 0.062 | 500 |
| 17W12519 | 17W12519B | 0.886 | 1.250 | 0.105 | 500 |
| 17W11256 | 17W11256B | 0.889 | 1.125 | 0.060 | 1000 |
| 17W11259* | 17W11259B | 0.920 | 1.125 | 0.126 | 500 |

| Item No. | | ID | OD | Thickness | Bulk Pack Qty |
|-------------|--------------|-------|-------|-----------|---------------|
| Natural | Black | in | in | in | |
| 17W17500* | 17W17500B | 0.928 | 1.750 | 0.275 | 500 |
| 17W13755* | 17W13755B | 0.938 | 1.310 | 0.040 | 1000 |
| 17W16253 | 17W16253B | 0.940 | 1.625 | 0.060 | 500 |
| 17W11320* | 17W11320B | 0.942 | 1.132 | 0.130 | 500 |
| 17W18001 | 17W18001B | 0.948 | 1.800 | 0.057 | 500 |
| 17W12031 | 17W12031B | 0.984 | 1.203 | 0.050 | 500 |
| MFW150A | — | 0.984 | 1.732 | 0.157 | 250 |
| 17W14502 | 17W14502B | 0.990 | 1.450 | 0.120 | 1000 |
| 17W13120 | 17W13120B | 1.000 | 1.312 | 0.191 | 500 |
| 17W13122 | 17W13122B | 1.000 | 1.312 | 0.125 | 1000 |
| 17W14371 | 17W14371B | 1.000 | 1.437 | 0.069 | 1000 |
| 17W14501 | 17W14501B | 1.000 | 1.450 | 0.063 | 1000 |
| 17W15620 | 17W15620B | 1.000 | 1.563 | 0.062 | 1000 |
| 17W16252 | 17W16252B | 1.000 | 1.625 | 0.187 | 500 |
| 17W22500 | 17W22500B | 1.000 | 2.250 | 0.075 | 250 |
| 17W12251 | 17W12251B | 1.001 | 1.245 | 0.031 | 500 |
| 17W15014 | 17W15014B | 1.010 | 1.468 | 0.112 | 1000 |
| 17W13759 | 17W13759B | 1.015 | 1.375 | 0.125 | 500 |
| 17W10018 | 17W10018B | 1.015 | 1.500 | 0.250 | 250 |
| 17W15008 | 17W15008B | 1.015 | 1.500 | 0.080 | 1000 |
| 17W17243 | 17W17243B | 1.015 | 1.755 | 0.062 | 500 |
| 17W10627* | 17W10627B | 1.022 | 1.135 | 0.500 | 500 |
| 17W13125 | 17W13125B | 1.026 | 1.312 | 0.191 | 500 |
| 17W18500 | 17W18500B | 1.028 | 1.850 | 0.120 | 500 |
| 17W12181 | 17W12181B | 1.031 | 1.218 | 0.040 | 1000 |
| 17W13762* | 17W13762B | 1.031 | 1.375 | 0.500 | 1000 |
| 17W25001 | 17W25001B | 1.075 | 2.500 | 0.125 | 250 |
| 17W20004 | 17W20004B | 1.080 | 2.000 | 0.160 | 250 |
| 17W13121 | 17W13121B | 1.088 | 1.312 | 0.062 | 500 |
| MFW160A | — | 1.102 | 1.969 | 0.157 | 250 |
| 17W29503 | 17W29503B | 1.125 | 2.935 | 0.093 | 250 |
| 17W15400 | 17W15400B | 1.164 | 1.540 | 0.192 | 500 |
| 17W14610 | 17W14610B | 1.180 | 1.460 | 0.100 | 1000 |
| MFW170A | — | 1.220 | 2.205 | 0.157 | 250 |
| 17W15021* | 17W15021B | 1.230 | 1.500 | 0.064 | 500 |
| 17W15009 | 17W15009B | 1.250 | 1.500 | 0.125 | 1000 |
| 17W16900 | 17W16900B | 1.255 | 1.695 | 0.065 | 1000 |
| 17W30000 | 17W30000B | 1.270 | 3.005 | 0.093 | 250 |
| 17W22800 | 17W22800B | 1.275 | 2.275 | 0.120 | 250 |
| 17W20001 | 17W20001B | 1.280 | 2.010 | 0.135 | 250 |
| 17W20013 | 17W20013B | 1.325 | 2.000 | 0.310 | 250 |
| 17W16251 | 17W16251B | 1.375 | 1.625 | 0.110 | 500 |
| 17W16514* | 17W16514B | 1.395 | 1.650 | 0.140 | 500 |
| 17W16300* | 17W16300B | 1.405 | 1.635 | 0.093 | 500 |
| 17W20014* | 17W20014B | 1.410 | 2.250 | 0.130 | 250 |
| 17W21850* | 17W21850B | 1.420 | 2.180 | 0.050 | 250 |
| MFW180A | — | 1.457 | 2.598 | 0.197 | 250 |
| 17W30002* | 17W30002B | 1.490 | 2.970 | 0.125 | 250 |
| 17W16240* | 17W16240B | 1.495 | 1.619 | 0.245 | 500 |
| 17W17241 | 17W17241B | 1.500 | 1.724 | 0.032 | 1000 |
| 17W19060 | 17W19060B | 1.500 | 1.906 | 0.093 | 500 |
| 17W16301* | 17W16301B | 1.508 | 1.628 | 0.072 | 500 |
| 17W20012 | 17W20012B | 1.525 | 1.985 | 0.125 | 1000 |
| 17W20003 | 17W20003B | 1.525 | 2.000 | 0.060 | 250 |
| MFW190A | — | 1.575 | 2.835 | 0.236 | 250 |
| 17W30093 | 17W30093B | 1.625 | 3.005 | 0.093 | 250 |
| 17W22005* | 17W22005B | 1.720 | 2.205 | 0.050 | 250 |
| 17W25003 | 17W25003B | 1.750 | 2.500 | 0.125 | 250 |
| 17W21350* | 17W21350B | 1.760 | 0.453 | 0.130 | 250 |
| 17W20600* | 17W20600B | 1.800 | 2.060 | 0.055 | 250 |
| 17W26802 | 17W26802B | 1.930 | 2.690 | 0.125 | 250 |
| 17W32600* | 17W32600B | 2.620 | 3.260 | 0.062 | 250 |
| 16M70074500 | 16M70074500B | 2.756 | 2.933 | 0.197 | 1000 |
| 17W30003 | 17W30003B | 2.800 | 3.016 | 0.122 | 250 |
| 17W30073 | 17W30073B | 2.800 | 3.016 | 0.072 | 250 |
| 17W30300* | 17W30300B | 3.030 | 3.600 | 0.075 | 250 |

* Parts marked with * are non-standard, non-stocked items and will require a minimum order amount of \$1,000.