


## Internal Digital Caliper Gauge

Item number: 209-934

### Images



### Description


- Digital Caliper Gauge enables measurements in hard-to-reach places
- Excellent resistance against water and dust IP67 level

### Features

<b>Digital/Analog:</b>	Digital
<b>Functions:</b>	Measuring contacts: carbide bevel (R = 0,1 mm)
<b>Delivered:</b>	Including 2 batteries LR3, certificate of inspection
<b>Range:</b>	2.5 - 12.5 mm
<b>Type:</b>	Fig. 1


<b>Digital step:</b>	0,001 / 0,002 / 0,005 / 0,01 / 0,02 / 0,05 mm
<b>Protection:</b>	IP67
<b>Measuring force:</b>	0,8-1,2 N
<b>Mass:</b>	245 g
<b>Power supply:</b>	2 batteries LR3 (AAA)
<b>ABS/INC switchable:</b>	Yes
<b>Auto Power OFF after 1/5/10 min. non use:</b>	YES
<b>OFFSET:</b>	Yes
<b>mm/inch conversion:</b>	Yes
<b>HOLD:</b>	Yes
<b>SET key:</b>	Yes
<b>DATA key:</b>	Yes
<b>DATA-Logger (100 measured values):</b>	Yes
<b>Max. reading:</b>	Yes
<b>Min. reading:</b>	Yes
<b>Tolerance LED (green/red):</b>	Yes
<b>Tolerance judgement:</b>	Yes

## Dimensions



## Accessories

Optional accessories:



**Digimatic Interface Series 209**

Digital Caliper Gauge  
 Art No. 011551  
 Suggested retail price: 90.00 €\*

Promotion!

Mitutoyo

MiCAT

the standard in world  
metrology software  
MeasurLink®


### USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Promo price: **259.00 €\***

Suggested retail price: ~~340.00 €\*~~



### Digimatic Cable, Round 6-Pin Type

1m

Art No. 937387

Suggested retail price: **60.00 €\***



### Digimatic Cable, Round 6-Pin Type

2m

Art No. 965013

Suggested retail price: **72.00 €\***

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Round 6-Pin Type

Art No. 06AFM380E

Promo price: **98.90 €\***

Suggested retail price: ~~124.00 €\*~~

Promotion!



### U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: **129.00 €\***

Suggested retail price: ~~187.00 €\*~~

Promotion!



### U-WAVE-T, Buzzer Type

Wireless Transmitter

Art No. 02AZD880G

Promo price: **129.00 €\***

Suggested retail price: ~~187.00 €\*~~

Promotion!




### Connection Cable E for U-WAVE

Round 6-Pin Type

Art No. 02AZD790E

Promo price: **63.90 €\***

Suggested retail price: ~~98.00 €\*~~



### Holder for Digital Caliper Gauge

for 209-930 up to 209-958

Art No. 63AAA438

Suggested retail price: ~~189.00 €\*~~

#### Spare parts

Consumable spares:



### Battery LR03 (AAA)

4x

Art No. 011511-1

Price on application