

## Digital Micrometer IP65 Set

Item number: 293-966-30

### Images



Dust- and  
Water-  
Protected

[www.tuv.com](http://www.tuv.com)  
ID 0000040191



### Description

This IP65 Micrometer offers outstanding accuracy, with data output, is highly robust and offers the following benefits:

- Oil-resistant material used for all plastic parts
- Extraordinary battery life of 2,4 years
- Excellent resistance against water and dust enables this micrometer to be used in machining situations that include splashing coolant fluid.

### Features



|                           |  |
|---------------------------|--|
| <b>Digital/Analog:</b>    | Digital  |
| <b>Delivered:</b>         | Including box, spanner, SR44 battery, setting standards (1 pcs.), certificate of inspection (2 pcs.) |
| <b>Inch-Metric:</b>       | Metric   |
| <b>Range:</b>             | 0 - 50 mm  |
| <b>Digital step:</b>      | 0.001 mm   |
| <b>Data output:</b>       | Yes  |
| <b>Display:</b>           | LCD, character height 7.5 mm   |
| <b>Measuring face:</b>    | Carbide-tipped, micro-lap finish   |
| <b>Measuring spindle:</b> | With spindle lock, $\varnothing 6.35$ mm, spindle pitch 0.5 mm                                       |

|  |  |
|--|--|
| <b>Scale:</b>                                | Thimble and sleeve satin chrome finish, ø18 mm                                 |
| <b>Measuring force:</b>                      | 5 - 10 N   |
| <b>Power supply:</b>                         | 1 battery SR-44  |
| <b>Battery life:</b>                         | Approx. 2.4 years  |
| <b>Content of Set:</b>                       | 293-230-30 / 293-231-30 + setting standard 25 mm (ceramic gauge block grade 1) |
| <b>ABS / INC (INC ZERO):</b>                 | Yes  |
| <b>Auto Power OFF after 20 min. non use:</b> | Yes  |
| <b>Low voltage alarm:</b>                    | Yes  |
| <b>Function lock:</b>                        | Yes  |
| <b>HOLD:</b>                                 | Yes  |
| <b>Mass:</b>                                 | 1030 g   |

## Accessories

### Optional accessories:

Promotion!





the standard in world metrology software  
**measurLink**

### USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)  
Art No. 06AGR543

**Promo price: 259.00 €\***   
~~Suggested retail price: 340.00 €\*~~





### Digimatic Cable with Data Button IP Type

1m, Micrometer Type  
Art No. 05CZA662  
Suggested retail price: 105.00 €\*



### Digimatic Cable with Data Button IP Type

2m, Micrometer Type  
Art No. 05CZA663  
Suggested retail price: 107.00 €\*

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data  
Button IP Micrometer Type  
Art No. 06AFM380B

Promo price: **109.00 €\***

Suggested retail price: ~~141.00 €\*~~

Promotion!



### U-WAVE fit, IP67 Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-622

Promo price: **129.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit, Buzzer Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-623

Promo price: **129.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-626

Promo price: **139.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-627

Promo price: **139.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### Connection Unit for IP Caliper, Micrometer

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth

Art No. 02AZF310

Promo price: **74.90 €\***

Suggested retail price: ~~110.00 €\*~~

Promotion!



### Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **55.90 €\***

Suggested retail price: ~~70.00 €\*~~

#### Standard accessories:



### Gauge Block, Metric, Inspection Cert.

ISO, Grade 1, Ceramic, 25mm

Art No. 613635-031

Suggested retail price: **119.00 €\***

#### Spare parts

#### Consumable spares:



### Battery SR44 1,5 V

Art No. 938882

Suggested retail price: **10.00 €\***

