

## Digital Disc Micrometer

### QuickMike, IP65

Item number: 369-422-20

#### Images



**ABSOLUTE<sup>®</sup>**  
**IP65**

#### Description

The ABSOLUTE Digimatic Disc Micrometer Quickmike allows you to measure with a fast spindle feed of 10 mm per thimble rotation.

It offers you the following benefits:


- Suitable for measuring felt, rubber, cardboard, fabric etc.
- Suitable to measure "root tangent length" of spur gears and helical gears.
- With a non-rotating spindle and disc-shaped measuring surface.
- Measuring force is adjustable for various kinds of workpieces (series 227)

#### Features

<b>Digital/Analog:</b>	Digital
<b>Inch-Metric:</b>	Inch/Metric
<b>Range:</b>	1 - 2.2 "
<b>Digital step:</b>	0.00005"/0.001 mm
<b>Max. Permissible Error J MPE:</b>	±0.0002"
<b>Delivered:</b>	Including box, setting standard, 1 SR44 battery
<b>Parallelism:</b>	0.0002"
<b>Display:</b>	LCD, character height 10 mm
<b>Measuring face:</b>	Hardened steel, micro-lap finish

<b>Measuring spindle:</b>	ø6,35 mm, non-rotating, spindle feed 10 mm
<b>Data output:</b>	Yes
<b>Power supply:</b>	1 battery SR-44
<b>Battery life:</b>	Approx. 5 years
<b>Measurable module:</b>	0.5 - 6 mm
<b>ON/OFF:</b>	Yes
<b>ORIGIN:</b>	Yes
<b>ABS / INC (INC ZERO):</b>	Yes
<b>Low voltage alarm:</b>	Yes
<b>HOLD:</b>	Yes
<b>Mass:</b>	485 g

## Dimensions



**L:** 25 mm

**a:** 10.3 mm

**b:** 47 mm

**c:** 13.5 mm

## Accessories

Optional accessories:



### Micrometer Stand, 45° Angle Type

for Micrometer 0-50mm/0-2"

Art No. 156-105-10

Suggested retail price: 58.00 €\*

Promotion!



### Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **56.00 €\***

Suggested retail price: 70.00 €\*

Promotion!



### Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type  
Art No. 02AZD790B

Promo price: **76.00 €\***

Suggested retail price: ~~110.00 €\*~~

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type  
Art No. 06AFM380B

Promo price: **111.00 €\***

Suggested retail price: ~~141.00 €\*~~

### Digimatic Cable with Data Button IP Type



1 m, Micrometer Type

Art No. 05CZA662

Suggested retail price: 105.00 €\*

### Digimatic Cable with Data Button IP Type



2 m, Micrometer Type

Art No. 05CZA663

Suggested retail price: 107.00 €\*

Promotion!



### U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: **129.00 €\***

Suggested retail price: ~~187.00 €\*~~

Promotion!



## U-WAVE-T, Buzzer Type

Wireless Transmitter

Art No. 02AZD880G

Promo price: **129.00 €\***

Suggested retail price: ~~187.00 €\*~~

### Standard accessories:



## Micrometer Setting Standard

Length: 1"

Art No. 167-141

Suggested retail price: **33.00 €\***

### Spare parts

#### Consumable spares:



## Battery SR44 1,5 V

Art No. 938882

Suggested retail price: **7.00 €\***