

## Digital 3-Point Internal Micrometer

Item number: 468-264

### Images



Dust- and  
Waterproof  
IP65

[www.tuv.com](http://www.tuv.com)  
ID 0000021605



### Description

A water-resistant Mitutoyo bore gauge comprising a digital/analogue display unit and measuring head. Suitable for measuring to the bottom of blind holes. Titanium-coated contact faces for enhanced durability. Digimatic data output. A ratchet stop guarantees repeatable measurement.


### Features

Digital/Analog:

Digital

<b>Inch-Metric:</b>	Inch/Metric
<b>Range:</b>	0,5-0,65" "
<b>Digital step:</b>	0.00005"
<b>Display:</b>	LCD, character height 7.5 mm
<b>Measuring face:</b>	Titanium-coated hardened steel taper: tungsten carbide
<b>Power supply:</b>	1 battery SR-44
<b>Battery life:</b>	Approx. 1.2 years
<b>ABS / INC (INC ZERO):</b>	Yes
<b>Auto Power OFF after 20 min. non use:</b>	Yes
<b>Low voltage alarm:</b>	Yes
<b>Function lock:</b>	Yes
<b>HOLD:</b>	Yes
<b>2 x PRESET:</b>	Yes
<b>Delivered:</b>	Including box, hex wrench, spanner, screwdriver, 1 SR44 battery, certificate of inspection
<b>Data output:</b>	Yes
<b>Mass:</b>	400 g

#### Dimensions



**L1:** 197.5 - 201.5 mm

**L2:** 84 mm

#### Accessories

Optional accessories:



#### Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **55.90 €\***

Suggested retail price: ~~70.00 €\*~~

Promotion!



## Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type

Art No. 02AZD790B

Promo price: **72.90 €\***

Suggested retail price: ~~110.00 €\*~~

Promotion!



## USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type

Art No. 06AFM380B

Promo price: **109.00 €\***

Suggested retail price: ~~141.00 €\*~~

## Digimatic Cable with Data Button IP Type



1m, Micrometer Type

Art No. 05CZA662

Suggested retail price: 105.00 €\*

## Digimatic Cable with Data Button IP Type



2m, Micrometer Type

Art No. 05CZA663

Suggested retail price: 107.00 €\*

## Holder for Micrometer Stand



for Series 468

Art No. 04AZB157

Suggested retail price: 62.00 €\*



## Holtest, Borematic Extension 150mm

for 12-20mm Measuring Range  
Art No. 952621  
Suggested retail price: 118.00 €\*



## Setting Ring 0,5"

Steel  
Art No. 177-180  
Suggested retail price: 120.00 €\*

Promotion!



## U-WAVE-T, IP67 Type

Wireless Transmitter  
Art No. 02AZD730G  
Promo price: **129.00 €\***  
Suggested retail price: 187.00 €\*

Promotion!



## U-WAVE-T, Buzzer Type

Wireless Transmitter  
Art No. 02AZD880G  
Promo price: **129.00 €\***  
Suggested retail price: 187.00 €\*

Promotion!

Mitutoyo

**MiCAT**  
the standard in world  
metrology software  
**MeasurLink**

## USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available  
Online)  
Art No. 06AGR543  
Promo price: **259.00 €\***  
Suggested retail price: 340.00 €\*

USB-ITPAK

Consumable spares:

---



**Battery SR44 1,5 V**

Art No. 938882

Suggested retail price: 10.00 €\*  

---