


Tubular Inside Micrometer with Extension

Item number: 139-179

Images




Description

A Mitutoyo inside micrometer covering a range of measurement by using a set of interchangeable extension tubes that can be used singly or in combination. The micrometer head is satin-chrome finished.

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Range:	4 - 36 "
Measuring span:	1"
Graduation:	0.001"
Limit of error:	$\pm(0,00015+0,00005 \times \text{number of rods} + 0,00005(\text{max. measurement length}/2))"$
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 18$ mm $\varnothing 13$ mm (139-203, 139-204)
Measuring spindle:	Spindle pitch 0,025" mm
Measuring face:	Carbide
Measuring method:	2-point
Extension rods:	5 (1, 2, 4, 8, 16")
Delivered:	Including box, spanner, extension rods (5 pcs.), micrometer head 139-002
Spindle feed error:	0.00015 inch
Mass:	790 g

Dimensions



Accessories

Standard accessories:

Main Unit for Tubular Inside Micrometer



Carbide Tipped 100-125mm
Art No. 139-001
Suggested retail price: 251.00 €*

Tubular Inside Micrometer 100-110mm



for 139-203
Art No. 139-003
Suggested retail price: 146.00 €*


Tubular Inside Micrometer 100-125mm



for 139-204
Art No. 139-005
Suggested retail price: 152.00 €*


Spare parts

Consumable spares:



Extension Rod for Series 139, 339

25mm
Art No. 981003
Suggested retail price: 60.00 €*



Extension Rod for Series 139, 339

50mm
Art No. 981005
Suggested retail price: 65.00 €*



Extension Rod for Series 139, 339

100mm
Art No. 981007
Suggested retail price: 136.00 €*



Extension Rod for Series 139, 339

200mm
Art No. 981009
Suggested retail price: 155.00 €*



Extension Rod for Series 139, 339

400mm
Art No. 981011
Suggested retail price: 182.00 €*



Extension Rod 10mm

for 139-203
Art No. 981981
Price on application

Extension Rod 20mm

for 139-203

Art No. 981982

Price on application



Extension Rod 30mm

for 139-203

Art No. 981983

Price on application



Extension Rod 60mm

for 139-203

Art No. 981984

Price on application



Extension Rod 90mm

for 139-203

Art No. 981985

Price on application



Extension Rod 110mm

for 139-203

Art No. 981986

Price on application



Extension Rod 120mm

for 139-203

Art No. 981987

Price on application



Extension Rod 130mm

for 139-203

Art No. 981988

Price on application



Extension Rod 25mm

for 139-204

Art No. 981991

Price on application



Extension Rod 75mm

for 139-204

Art No. 981993

Price on application



Extension Rod 150mm

for 139-204

Art No. 981994

Price on application



Extension Rod 225mm

for 139-204

Art No. 981995

Price on application



Extension Rod 300mm

for 139-204

Art No. 981996

Price on application



Extension Rod 350mm

for 139-204

Art No. 981997

Price on application



Extension Rod 400mm

for 139-204

Art No. 981998

Price on application



Extension Rod 425mm

for 139-204

Art No. 981999

Price on application



Extension Rod 450mm

for 139-204

Art No. 982000

Price on application

