

## Digital 3-Point Internal Micrometer Set

Item number: 468-989

### Images



Dust- and  
Waterproof  
IP65

www.tuv.com  
ID 0000021605



### Description


Des

### Features

<b>Digital/Analog:</b>	Digital
<b>Inch-Metric:</b>	Inch/Metric
<b>Range:</b>	2 - 3 "
<b>Digital step:</b>	0.001 mm, 0.001 mm/0.00005" (models up to 4") / 0.001 mm/0.0001" (models over 5")

<b>Individual ranges:</b>	2-2.5", 2.5-3"
<b>Display:</b>	LCD, character height 7.5 mm
<b>Measuring face:</b>	Titanium coated tungsten carbide (6-12 mm) Titanium coated hardened steel (12-100 mm) Taper: tungsten carbide
<b>Models included:</b>	468-270 / 468-271
<b>Setting rings included:</b>	ø2.5" (177-315)
<b>Power supply:</b>	1 battery SR-44
<b>Battery life:</b>	Approx. 1.2 years
<b>ABS / INC (INC ZERO):</b>	Yes
<b>Auto Power OFF after 20 min. non use:</b>	Yes
<b>Low voltage alarm:</b>	Yes
<b>Function lock:</b>	Yes
<b>HOLD:</b>	Yes
<b>2 x PRESET:</b>	Yes
<b>Delivered:</b>	Including box, hex wrench, spanner (2 pcs.), screwdriver, 1 SR44 battery, setting ring (1 pcs.), extension rod, certificate of inspection
<b>Data output:</b>	Yes
<b>Mass:</b>	1270 g

## Dimensions



**L1:** 219.6 - 232.6 mm

**L2:** 105.4 mm

## Accessories

### Optional accessories:

Promotion!




the standard in world  
metrology software  
**MeasurLink**

### USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

**Promo price: 259.00 €\***

Suggested retail price: ~~340.00 €\*~~



USB-ITPAK



### Digimatic Cable with Data Button IP Type

1m, Micrometer Type  
Art No. 05CZA662  
Suggested retail price: 105.00 €\*  
~~105.00 €\*~~



### Digimatic Cable with Data Button IP Type

2m, Micrometer Type  
Art No. 05CZA663  
Suggested retail price: 107.00 €\*  
~~107.00 €\*~~

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type  
Art No. 06AFM380B  
Promo price: **109.00 €\***  
Suggested retail price: ~~141.00 €\* 141.00 €\*~~

Promotion!



### U-WAVE-T, Buzzer Type

Wireless Transmitter  
Art No. 02AZD880G  
Promo price: **129.00 €\***  
Suggested retail price: ~~187.00 €\* 187.00 €\*~~

Promotion!



### U-WAVE-T, IP67 Type

Wireless Transmitter  
Art No. 02AZD730G  
Promo price: **129.00 €\***  
Suggested retail price: ~~187.00 €\* 187.00 €\*~~

Promotion!



## Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type  
Art No. 02AZD790B

Promo price: **72.90 €\***

Suggested retail price: ~~110.00 €\*~~

Promotion!



## Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"  
Art No. 156-101-10

Promo price: **55.90 €\***

Suggested retail price: ~~70.00 €\*~~

## Holder for Micrometer Stand

for Series 468

Art No. 04AZB157

Suggested retail price: **62.00 €\***



## Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range

Art No. 952623

Suggested retail price: **222.00 €\***

### Spare parts

Consumable spares:



## Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 10.00 €\*  

---