

2-Point Inside Measuring Instrument

Item number: 511-213-20

Images



Description


These are bore gauges that automatically self-centre via a centring bridge. They offer you the following benefits:

- A long plunger stroke gives you amazing accuracy.
- Interchangeable washers 0.5 mm thick are supplied as standard accessories, so you can enable setting in small steps.
- Contact points are carbide (>18 mm range), giving you high durability and wear resistance.
- A large grip reduces heat transfer from the operator by 50%.

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Range:	0.24 - 0.4 "
Graduation:	0.0005"
Stroke of contact point:	0.5 mm
Measuring depth:	2"
No. Dial Indicator:	2922SB
Number of anvils:	9
Accuracy:	5 μ m
Repeatability:	2 μ m
Measuring force:	\leq 2 N
Delivered:	In a box with bore gauge 511-214, dial indicator 2922AB, plastic cover for indicator 21DZA000, 9 anvils
Mass:	260 g

Dimensions



Accessories

Optional accessories:



Digital Indicator, Bore Gauge ID-C

ASME/ANSI Type, Inch/Metric, 0,5", 0,00005", Flat Back Plate

Art No. 543-312B-10

Suggested retail price: 563.00 €*



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application

Standard accessories:



Anvil (6 mm)/511

Small Holes Type, 6 mm/0,24 "

Art No. 952168

Price on application



Anvil (6.5mm)/511

Art No. 952169

Price on application



Anvil (7mm)/511

Art No. 952170

Price on application



Anvil (7.5mm)/511

Art No. 952414

Price on application



Anvil (8mm)/511

Art No. 952415

Price on application



Anvil (8.5mm)/511

Art No. 952416

Price on application

Anvil (9MM)/511

Art No. 952417

Price on application



Anvil (9.5mm)/511

Art No. 952418

Price on application



Anvil (10mm)/511

Art No. 952419

Price on application




206709

Spanner/511

Art No. 206709

Price on application



Tweezers/511

Art No. 206710


Price on application





Dial Gauge, Flat Back, ANSI/AGD Type

0,125", 0,0005"
Art No. 2922AB
Suggested retail price: 107.00 €*



2-Point Inside Measuring Instrument

Bore Gauge, 0,24-0,4", w/o Indicator
Art No. 511-214
Suggested retail price: 436.00 €*



Protector for Indicator (plastic cover)

Art No. 21DZA000
Suggested retail price: 20.00 €*