


# 2-Point Inside Measuring Instrument

Item number: 511-426-20

## Images



## Description


This is a bore gauge for measuring blind holes that offers you the following benefits:

- You can measure the inside diameter close to the bottom of blind holes.
- Contact points are carbide giving you high durability and wear resistance.

## Features

<b>Inch-Metric:</b>	Metric
<b>Digital/Analog:</b>	Analog
<b>Range:</b>	35 - 60 mm
<b>Graduation:</b>	0.01 mm
<b>Stroke of contact point:</b>	1.2 mm
<b>Measuring depth:</b>	150 mm
<b>No. Dial Indicator:</b>	2046AB
<b>Accuracy:</b>	4 $\mu$ m
<b>Repeatability:</b>	1 $\mu$ m
<b>Delivered:</b>	In a box with bore gauge 511-416, dial indicator 2046AB, plastic cover for indicator 21DZA000, 6 anvils, 4 interchangeable washer
<b>Mass:</b>	370 g

## Dimensions



## Accessories

Optional accessories:

### Extension Rod Serie 511

125mm, 9mm Rod Diameter  
Art No. 953549  
Suggested retail price: 230.00 €\*  

---



### Extension Rod Serie 511

250mm, 9mm Rod Diameter  
Art No. 953550  
Suggested retail price: 257.00 €\*  

---



### Extension Rod Serie 511

500mm, 9mm Rod Diameter  
Art No. 953551  
Suggested retail price: 399.00 €\*  

---



### Digital Indicator, Bore Gauge ID-C

12,7mm, 0,001mm, Flat Back Plate  
Art No. 543-310B-10  
Suggested retail price: 563.00 €\*  

---

### Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4  
Art No. 21AZB195  
Price on application  

---



## 2-Point Inside Measuring Instrument



Bore Gauge for Blind Holes, 35-60mm, w/o Indicator

Art No. 511-416

Suggested retail price: 438.00 €\*  
~~438.00 €\*  
438.00 €\*~~

Promotion!



## Dial Gauge, Flat Back, ISO Type

10mm, 0,01mm

Art No. 2046AB

Promo price: **37.90 €\*  
~~48.00 €\*~~**

Suggested retail price: 48.00 €\*



## Protector for Indicator (plastic cover)

Art No. 21DZA000

Suggested retail price: 20.00 €\*  
~~20.00 €\*~~

## ANVIL NO.1 FOR BORE GAGE

511-4xx

Art No. 21DZA404A

Price on application



## ANVIL NO.2 FOR BORE GAGE

511-4xx

Art No. 21DZA404B

Price on application





### ANVIL NO.3 FOR BORE GAGE

511-4xx  
Art No. 21DZA404C  
[Price on application](#)



### ANVIL NO.4 FOR BORE GAGE

511-4XX  
Art No. 21DZA404D  
[Price on application](#)



### ANVIL NO.5 FOR BORE GAGE

511-4xx  
Art No. 21DZA404E  
[Price on application](#)



### ANVIL NO.6 FOR BORE GAGE

511-4xx  
Art No. 21DZA404F  
[Price on application](#)



### Washer 0.5mm/.02"/511

Art No. 212127  
[Price on application](#)



### Washer 1mm/.04\"/>511

Art No. 212128

Price on application



### Washer 2mm/.08\"/>511

Art No. 212129

Price on application



### Washer 3mm/.12\"/>511

Art No. 212130

Price on application



### Spanner/511

Art No. 204354

Price on application