


2-Point Inside Measuring Instrument

Item number: 511-427-20

Images



Description


This is a bore gauge for measuring blind holes that offers you the following benefits:

- You can measure the inside diameter close to the bottom of blind holes.
- Contact points are carbide giving you high durability and wear resistance.

Features

Inch-Metric:	Metric
Digital/Analog:	Analog
Range:	50 - 150 mm
Graduation:	0.01 mm
Stroke of contact point:	1.2 mm
Measuring depth:	150 mm
No. Dial Indicator:	2046AB
Accuracy:	4 μ m
Repeatability:	1 μ m
Delivered:	In a box with bore gauge 511-417, dial indicator 2046AB, plastic cover for indicator 21DZA000, 11 anvils, 4 interchangeable washer
Mass:	380 g

Dimensions



a: 22.7 mm

b: 22 mm

Accessories

Optional accessories:

Extension Rod Serie 511

125mm, 9mm Rod Diameter
Art No. 953549
Suggested retail price: 230.00 €*



Extension Rod Serie 511

250mm, 9mm Rod Diameter
Art No. 953550
Suggested retail price: 257.00 €*



Extension Rod Serie 511

500mm, 9mm Rod Diameter
Art No. 953551
Suggested retail price: 399.00 €*



Digital Indicator, Bore Gauge ID-C

12,7mm, 0,001mm, Flat Back Plate
Art No. 543-310B-10
Suggested retail price: 563.00 €*



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application

2-Point Inside Measuring Instrument



Bore Gauge for Blind Holes, 50-150mm, w/o Indicator

Art No. 511-417

Suggested retail price: 580.00 €*

Promotion!



Dial Gauge, Flat Back, ISO Type

10mm, 0,01mm

Art No. 2046AB

Promo price: **37.90 €***

Suggested retail price: 48.00 €*



Protector for Indicator (plastic cover)

Art No. 21DZA000

Suggested retail price: 20.00 €*

ANVIL NO.1 FOR BORE GAGE

511-4xx

Art No. 21DZA404A

Price on application



ANVIL NO.2 FOR BORE GAGE

511-4xx

Art No. 21DZA404B

Price on application





ANVIL NO.3 FOR BORE GAGE

511-4xx
Art No. 21DZA404C
[Price on application](#)



ANVIL NO.4 FOR BORE GAGE

511-4XX
Art No. 21DZA404D
[Price on application](#)



ANVIL NO.5 FOR BORE GAGE

511-4xx
Art No. 21DZA404E
[Price on application](#)



ANVIL NO.6 FOR BORE GAGE

511-4xx
Art No. 21DZA404F
[Price on application](#)



ANVIL NO.7 FOR BORE GAGE

511-4xx
Art No. 21DZA404G
[Price on application](#)

ANVIL NO.8 FOR BORE GAGE

511-4xx
Art No. 21DZA404H
[Price on application](#)



ANVIL NO.9 FOR BORE GAGE

511-4xx
Art No. 21DZA404J
[Price on application](#)



ANVIL NO.10 FOR BORE GAG

E 511-4xx
Art No. 21DZA404L
[Price on application](#)



ANVIL NO.11 FOR BORE GAG

E 511-4xx
Art No. 21DZA404M
[Price on application](#)



Washer 0.5mm/.02"/511

Art No. 212127
[Price on application](#)





Washer 1mm/.04\"/>511

Art No. 212128

Price on application



Washer 2mm/.08\"/>511

Art No. 212129

Price on application



Washer 3mm/.12\"/>511

Art No. 212130

Price on application



SUB ANVIL FOR BORE GAGE

Art No. 21DAA596

Price on application



Spanner/511

Art No. 204354

Price on application