


## 2-Point Inside Measuring Instrument

Item number: 511-723-20

### Images



### Description

This is a short range application Bore Gauge Set that automatically self-centres via a centring bridge and offers you the following benefits:

- It reduces the influence of heat from the operator's hand by 50% by making the grip hollow structured, thereby retaining high accuracy measurement.
- Interchangeable washers (0,5 mm thick) are supplied as standard accessories, so you can enable setting in small steps.
- Contact points are carbide (>18 mm range), giving you high durability and wear resistance.

### Features

<b>Inch-Metric:</b>	Metric
<b>Range:</b>	50 - 150 mm



### Extension Rod Serie 511

500mm, 12mm Rod Diameter  
Art No. 953554  
Suggested retail price: 493.00 €\*  

---



### Extension Rod Serie 511

750mm, 12mm Rod Diameter  
Art No. 953555  
Suggested retail price: 655.00 €\*  

---



### Extension Rod Serie 511

1000mm, 12mm Rod Diameter  
Art No. 953556  
Suggested retail price: 907.00 €\*  

---



### Digital Indicator, Bore Gauge ID-C

12,7mm, 0,001mm, Flat Back Plate  
Art No. 543-310B-10  
Suggested retail price: 563.00 €\*  

---



### Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4  
Art No. 21AZB195  
Price on application  

---





### Carbide Tipped Anvil Series 511

Range 50mm (100mm)  
Art No. 21DZA232A  
Suggested retail price: 13.00 €\*



### Carbide Tipped Anvil Series 511

Range 40mm, 55mm (105mm)  
Art No. 21DZA232B  
Suggested retail price: 13.00 €\*



### Carbide Tipped Anvil Series 511

Range 45mm, 60mm (110mm)  
Art No. 21DZA232C  
Suggested retail price: 13.00 €\*



### Carbide Tipped Anvil Series 511

Range 50mm, 65mm (115mm)  
Art No. 21DZA232D  
Suggested retail price: 13.00 €\*



### Carbide Tipped Anvil Series 511

Range 55mm, 70mm (120mm)  
Art No. 21DZA232E  
Suggested retail price: 13.00 €\*



### **Carbide Tipped Anvil Series 511**

Range 60mm, 75mm (125mm)  
Art No. 21DZA232F  
Suggested retail price: 13.00 €\*  

---



### **Carbide Tipped Anvil Series 511**

Range 80mm (130mm)  
Art No. 21DZA232G  
Suggested retail price: 15.00 €\*  

---



### **Carbide Tipped Anvil Series 511**

Range 85mm (135mm)  
Art No. 21DZA232H  
Suggested retail price: 15.00 €\*  

---



### **Carbide Tipped Anvil Series 511**

Range 90mm (140mm)  
Art No. 21DZA232J  
Suggested retail price: 16.00 €\*  

---



### **Carbide Tipped Anvil Series 511**

Range 95mm (145mm)  
Art No. 21DZA232L  
Suggested retail price: 16.00 €\*  

---



## Carbide Tipped Anvil Series 511

Range 100mm (150mm)  
Art No. 21DZA232M  
Suggested retail price: 16.00 €\*



## Washer Series 511

0,5mm, Range 35-160mm  
Art No. 205457  
Suggested retail price: 7.00 €\*



## Washer Series 511

1 mm, Range 35-160mm  
Art No. 205458  
Suggested retail price: 7.00 €\*




## Washer Series 511

2 mm, Range 35-160mm  
Art No. 205459  
Suggested retail price: 7.00 €\*



## Washer Series 511

3 mm, Range 35-160mm  
Art No. 205460  
Suggested retail price: 7.00 €\*



### Sub-Anvil Series 511

50 mm  
Art No. 102178  
Suggested retail price: 24.00 €\*



### 2-Point Inside Measuring Instrument

Bore Gauge, 50-150mm, w/o Indicator  
Art No. 511-703  
Suggested retail price: 310.00 €\*



### Dial Gauge, Flat Back, ISO Type

Jewelled Bearing, Shockproof, 1mm,  
0,001mm  
Art No. 2109AB-10  
Suggested retail price: 106.00 €\*



### Protector for Indicator (plastic cover)

Art No. 21DZA000  
Suggested retail price: 20.00 €\*