


## 2-Point Inside Measuring Instrument

Item number: 511-741-20

### Images



### Description

This is a short range application Bore Gauge Set that automatically self-centres via a centring bridge and offers you the following benefits:


- It reduces the influence of heat from the operator's hand by 50% by making the grip hollow structured, thereby retaining high accuracy measurement.
- Interchangeable washers (0,5 mm thick) are supplied as standard accessories, so you can enable setting in small steps.
- Contact points are carbide (>18 mm range), giving you high durability and wear resistance.

### Features

<b>Inch-Metric:</b>	Inch
<b>Range:</b>	0.7 - 1.4 "

<b>Graduation:</b>	0.0005"
<b>Stroke of contact point:</b>	18 - 60 mm: 1.2 mm 50 - 400 mm: 1.6 mm
<b>Measuring depth:</b>	4"
<b>No. Dial Indicator:</b>	2922AB
<b>Number of anvils:</b>	9
<b>Accuracy:</b>	2 µm
<b>Repeatability:</b>	0.5 µm
<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a box with bore gauge 511-731, dial indicator 2922AB, plastic cover for indicator 21DZA000, 9 anvils, 2 interchangeable washer, spanner 102148
<b>Mass:</b>	330 g

## Dimensions



## Accessories

### Optional accessories:



### Digital Indicator, Bore Gauge ID-C


ASME/ANSI Type, Inch/Metric, 0,5", 0,00005",  
Flat Back Plate  
Art No. 543-312B-10  
Suggested retail price: 563.00 €\*  
\*




### Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4  
Art No. 21AZB195  
Price on application


### Extension Rod Serie 511

125mm, 9mm Rod Diameter  
Art No. 953549  
Suggested retail price: 230.00 €\*  


### Extension Rod Serie 511

250mm, 9mm Rod Diameter  
Art No. 953550  
Suggested retail price: 257.00 €\*  



### Extension Rod Serie 511

500mm, 9mm Rod Diameter  
Art No. 953551  
Suggested retail price: 399.00 €\*  



#### Standard accessories:



### Carbide Tipped Anvil Series 511

Range 18 mm  
Art No. 21DZA213A  
Suggested retail price: 11.00 €\*  


### Carbide Tipped Anvil Series 511

Range 20 mm  
Art No. 21DZA213B  
Suggested retail price: 11.00 €\*  




### **Carbide Tipped Anvil Series 511**

Range 22 mm  
Art No. 21DZA213C  
Suggested retail price: 11.00 €\*  


---



### **Carbide Tipped Anvil Series 511**

Range 24 mm  
Art No. 21DZA213D  
Suggested retail price: 12.00 €\*  


---



### **Carbide Tipped Anvil Series 511**

Range 26 mm  
Art No. 21DZA213E  
Suggested retail price: 12.00 €\*  


---



### **Carbide Tipped Anvil Series 511**

Range 28 mm  
Art No. 21DZA213F  
Suggested retail price: 12.00 €\*  

---



### **Carbide Tipped Anvil Series 511**

Range 30 mm  
Art No. 21DZA213G  
Suggested retail price: 13.00 €\*  

---



### **Carbide Tipped Anvil Series 511**

Range 32 mm  
Art No. 21DZA213H  
Suggested retail price: 13.00 €\*  

---



### **Carbide Tipped Anvil Series 511**

Range 34 mm  
Art No. 21DZA213J  
Suggested retail price: 13.00 €\*  

---



### **Washer Series 511**

0,5mm, Range 18-35mm  
Art No. 205623  
Suggested retail price: 7.00 €\*  

---



### **Washer Series 511**

1mm, Range 18-35mm  
Art No. 205624  
Suggested retail price: 7.00 €\*  

---



### **Spanner/526**

Art No. 102148  
Price on application  

---

## 2-Point Inside Measuring Instrument



Bore Gauge, 0,7-1,4", w/o Indicator  
Art No. 511-731  
Suggested retail price: 290.00 €\*  

---

## Dial Gauge, Flat Back, ANSI/AGD Type



0,125", 0,0005"  
Art No. 2922AB  
Suggested retail price: 107.00 €\*  

---

## Protector for Indicator (plastic cover)



Art No. 21DZA000  
Suggested retail price: 20.00 €\*  

---