

2-Point Inside Measuring Instrument

Item number: 511-766-20

Images



Description


This is a compact and lightweight bore gauge due to the short length below the grip. It offers you the following benefits:

- A long plunger stroke gives you amazing accuracy.
- Contact points are carbide giving you high durability and wear resistance.
- A large grip reduces heat transfer from the operator by 50%.

Features

Inch-Metric:	Metric
Range:	18 - 35 mm
Graduation:	0.01 mm
Stroke of contact point:	1.2 mm
Measuring depth:	50 mm
No. Dial Indicator:	2046AB
Number of anvils:	9
Accuracy:	2 μ m
Repeatability:	0.5 μ m
Digital/Analog:	Analog
Delivered:	In a box with bore gauge 511-761, dial indicator 2046AB, plastic cover for indicator 21DZA000, 9 anvils, 2 interchangeable washer, spanner 102148
Mass:	320 g

Dimensions



Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application




Digital Indicator, Bore Gauge ID-C

12,7mm, 0,001mm, Flat Back Plate

Art No. 543-310B-10

Suggested retail price: 563.00 €*

Standard accessories:



2-Point Inside Measuring Instrument

Bore Gauge for Short Length, 18-35mm, w/o Indicator

Art No. 511-761

Suggested retail price: 228.00 €*

Promotion!



Dial Gauge, Flat Back, ISO Type

10mm, 0,01mm

Art No. 2046AB

Promo price: **37.90 €***

Suggested retail price: ~~48.00 €*~~



Protector for Indicator (plastic cover)

Art No. 21DZA000

Suggested retail price: 20.00 €*



Carbide Tipped Anvil Series 511

Range 18 mm

Art No. 21DZA213A

Suggested retail price: 11.00 €*



Carbide Tipped Anvil Series 511

Range 20 mm

Art No. 21DZA213B

Suggested retail price: 11.00 €*



Carbide Tipped Anvil Series 511

Range 22 mm


Art No. 21DZA213C

Suggested retail price: 11.00 €*



Carbide Tipped Anvil Series 511

Range 24 mm
Art No. 21DZA213D
Suggested retail price: 12.00 €*



Carbide Tipped Anvil Series 511

Range 26 mm
Art No. 21DZA213E
Suggested retail price: 12.00 €*



Carbide Tipped Anvil Series 511

Range 28 mm
Art No. 21DZA213F
Suggested retail price: 12.00 €*



Carbide Tipped Anvil Series 511

Range 30 mm
Art No. 21DZA213G
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 32 mm
Art No. 21DZA213H
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 34 mm
Art No. 21DZA213J
Suggested retail price: 13.00 €*



Washer Series 511

0,5mm, Range 18-35mm
Art No. 205623
Suggested retail price: 7.00 €*



Washer Series 511

1mm, Range 18-35mm
Art No. 205624
Suggested retail price: 7.00 €*



Spanner/526

Art No. 102148
Price on application
