

## 2-Point Inside Measuring Instrument

Item number: 511-767-20

### Images



### Description


This is a compact and lightweight bore gauge due to the short length below the grip. It offers you the following benefits:

- A long plunger stroke gives you amazing accuracy.
- Contact points are carbide giving you high durability and wear resistance.
- A large grip reduces heat transfer from the operator by 50%.

### Features

<b>Inch-Metric:</b>	Metric
<b>Range:</b>	35 - 60 mm
<b>Graduation:</b>	0.01 mm
<b>Stroke of contact point:</b>	1.2 mm
<b>Measuring depth:</b>	50 mm
<b>No. Dial Indicator:</b>	2046AB
<b>Number of anvils:</b>	6
<b>Accuracy:</b>	2 $\mu$ m
<b>Repeatability:</b>	0.5 $\mu$ m
<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a box with bore gauge 511-762, dial indicator 2046AB, plastic cover for indicator 21DZA000, 6 anvils, 4 interchangeable washer, spanner 102148
<b>Mass:</b>	380 g

### Dimensions



## Accessories

### Optional accessories:



### Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



### Digital Indicator, Bore Gauge ID-C

12,7mm, 0,001mm, Flat Back Plate

Art No. 543-310B-10

Suggested retail price: 563.00 €\*

### Standard accessories:



### 2-Point Inside Measuring Instrument

Bore Gauge for Short Length, 35-60mm, w/o Indicator

Art No. 511-762

Suggested retail price: 250.00 €\*

Promotion!



## Dial Gauge, Flat Back, ISO Type

10mm, 0,01mm

Art No. 2046AB

Promo price: **37.90 €\***

Suggested retail price: ~~48.00 €\*~~



## Protector for Indicator (plastic cover)

Art No. 21DZA000

Suggested retail price: 20.00 €\*



## Carbide Tipped Anvil Series 511

Range 50mm (100mm)

Art No. 21DZA232A

Suggested retail price: 13.00 €\*



## Carbide Tipped Anvil Series 511

Range 40mm, 55mm (105mm)

Art No. 21DZA232B

Suggested retail price: 13.00 €\*



## Carbide Tipped Anvil Series 511

Range 45mm, 60mm (110mm)

Art No. 21DZA232C

Suggested retail price: 13.00 €\*

### **Carbide Tipped Anvil Series 511**



Range 50mm, 65mm (115mm)  
Art No. 21DZA232D  
Suggested retail price: 13.00 €\*  

---

### **Carbide Tipped Anvil Series 511**



Range 55mm, 70mm (120mm)  
Art No. 21DZA232E  
Suggested retail price: 13.00 €\*  

---

### **Carbide Tipped Anvil Series 511**



Range 60mm, 75mm (125mm)  
Art No. 21DZA232F  
Suggested retail price: 13.00 €\*  

---

### **Washer Series 511**



0,5mm, Range 35-160mm  
Art No. 205457  
Suggested retail price: 7.00 €\*  

---

### **Washer Series 511**



1 mm, Range 35-160mm  
Art No. 205458  
Suggested retail price: 7.00 €\*  

---



### Washer Series 511

2 mm, Range 35-160mm  
Art No. 205459  
Suggested retail price: 7.00 €\*  

---



### Washer Series 511

3 mm, Range 35-160mm  
Art No. 205460  
Suggested retail price: 7.00 €\*  

---