

## 2-Point Inside Measuring Instrument

Item number: 511-774-20

### Images



### Description


This is a compact and lightweight bore gauge due to the short length below the grip. It offers you the following benefits:

- A long plunger stroke gives you amazing accuracy.
- Contact points are carbide giving you high durability and wear resistance.
- A large grip reduces heat transfer from the operator by 50%.

### Features

<b>Inch-Metric:</b>	Metric
<b>Range:</b>	100 - 160 mm
<b>Graduation:</b>	0.001 mm
<b>Stroke of contact point:</b>	1.6 mm
<b>Measuring depth:</b>	50 mm
<b>No. Dial Indicator:</b>	2109AB-10
<b>Number of anvils:</b>	13
<b>Accuracy:</b>	2 $\mu$ m
<b>Repeatability:</b>	0.5 $\mu$ m
<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a box with bore gauge 511-764, dial indicator 2109AB-10, plastic cover for indicator 21DZA000, 13 anvils, 4 interchangeable washer
<b>Mass:</b>	460 g

### Dimensions



**Accessories**

**Optional accessories:**



**Limit Hands (green) 2pcs**

Dial Indicator Series 2/3/4  
 Art No. 21AZB195  
 Price on application



**Digital Indicator, Bore Gauge ID-C**

12,7mm, 0,001mm, Flat Back Plate  
 Art No. 543-310B-10  
 Suggested retail price: 563.00 €\*

**Standard accessories:**



**2-Point Inside Measuring Instrument**

Bore Gauge for Short Length, 100-160mm, w/o Indicator  
 Art No. 511-764  
 Suggested retail price: 435.00 €\*



### Dial Gauge, Flat Back, ISO Type

Jewelled Bearing, Shockproof, 1mm, 0,001mm  
Art No. 2109AB-10  
Suggested retail price: 106.00 €\*  
BCTRO5



### Protector for Indicator (plastic cover)

Art No. 21DZA000  
Suggested retail price: 20.00 €\*  
BCTRO5



### Carbide Tipped Anvil Series 511

Range 50mm (100mm)  
Art No. 21DZA232A  
Suggested retail price: 13.00 €\*  
BCTRO5



### Carbide Tipped Anvil Series 511

Range 40mm, 55mm (105mm)  
Art No. 21DZA232B  
Suggested retail price: 13.00 €\*  
BCTRO5



### Carbide Tipped Anvil Series 511

Range 45mm, 60mm (110mm)  
Art No. 21DZA232C  
Suggested retail price: 13.00 €\*  
BCTRO5

### **Carbide Tipped Anvil Series 511**



Range 50mm, 65mm (115mm)  
Art No. 21DZA232D  
Suggested retail price: 13.00 €\*

---

### **Carbide Tipped Anvil Series 511**



Range 55mm, 70mm (120mm)  
Art No. 21DZA232E  
Suggested retail price: 13.00 €\*

---

### **Carbide Tipped Anvil Series 511**



Range 60mm, 75mm (125mm)  
Art No. 21DZA232F  
Suggested retail price: 13.00 €\*

---

### **Carbide Tipped Anvil Series 511**



Range 80mm (130mm)  
Art No. 21DZA232G  
Suggested retail price: 15.00 €\*

---

### **Carbide Tipped Anvil Series 511**



Range 85mm (135mm)  
Art No. 21DZA232H  
Suggested retail price: 15.00 €\*

---



### Carbide Tipped Anvil Series 511

Range 90mm (140mm)  
Art No. 21DZA232J  
Suggested retail price: 16.00 €\*  

---



### Carbide Tipped Anvil Series 511

Range 95mm (145mm)  
Art No. 21DZA232L  
Suggested retail price: 16.00 €\*  

---



### Carbide Tipped Anvil Series 511

Range 100mm (150mm)  
Art No. 21DZA232M  
Suggested retail price: 16.00 €\*  

---



### Carbide Tipped Anvil Series 511

Range 155mm  
Art No. 21DZA232N  
Price on application  

---



### Carbide Tipped Anvil Series 511

Range 160mm  
Art No. 21DZA232P  
Price on application  

---



### Washer Series 511

0,5mm, Range 35-160mm  
Art No. 205457  
Suggested retail price: 7.00 €\*  

---



### Washer Series 511

1 mm, Range 35-160mm  
Art No. 205458  
Suggested retail price: 7.00 €\*  

---



### Washer Series 511

2 mm, Range 35-160mm  
Art No. 205459  
Suggested retail price: 7.00 €\*  

---



### Washer Series 511

3 mm, Range 35-160mm  
Art No. 205460  
Suggested retail price: 7.00 €\*  

---