

## 2-Point Inside Measuring Instrument

Item number: 511-788-20

### Images



### Description

This is a compact and lightweight bore gauge due to the short length below the grip. It offers you the following benefits:

- A long plunger stroke gives you amazing accuracy.
- Contact points are carbide giving you high durability and wear resistance.
- A large grip reduces heat transfer from the operator by 50%.


### Features

<b>Inch-Metric:</b>	Inch
<b>Range:</b>	2 - 6 "
<b>Graduation:</b>	0.0005"
<b>Stroke of contact point:</b>	18 - 60 mm: 1.2 mm 50 - 160 mm: 1.6 mm
<b>Measuring depth:</b>	2"
<b>No. Dial Indicator:</b>	2922AB
<b>Number of anvils:</b>	11
<b>Accuracy:</b>	2 $\mu$ m
<b>Repeatability:</b>	0.5 $\mu$ m
<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a box with bore gauge 511-783, dial indicator 2922AB, plastic cover for indicator 21DZA000, 11 anvils, 4 interchangeable washer, 1 sub-anvil

Mass:

400 g

## Dimensions



## Accessories

### Optional accessories:



### Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



### Digital Indicator, Bore Gauge ID-C

ASME/ANSI Type, Inch/Metric, 0,5", 0,00005", Flat Back Plate

Art No. 543-312B-10

Suggested retail price: 563.00 €\*

### Standard accessories:



### 2-Point Inside Measuring Instrument

Bore Gauge for Short Length, 2-6", w/o Indicator

Art No. 511-783

Suggested retail price: 295.00 €\*



### Dial Gauge, Flat Back, ANSI/AGD Type

0,125", 0,0005"  
Art No. 2922AB  
Suggested retail price: 107.00 €\*



### Protector for Indicator (plastic cover)

Art No. 21DZA000  
Suggested retail price: 20.00 €\*



### Carbide Tipped Anvil Series 511

Range 50mm (100mm)  
Art No. 21DZA232A  
Suggested retail price: 13.00 €\*



### Carbide Tipped Anvil Series 511

Range 40mm, 55mm (105mm)  
Art No. 21DZA232B  
Suggested retail price: 13.00 €\*



### Carbide Tipped Anvil Series 511

Range 45mm, 60mm (110mm)  
Art No. 21DZA232C  
Suggested retail price: 13.00 €\*

### **Carbide Tipped Anvil Series 511**



Range 50mm, 65mm (115mm)  
Art No. 21DZA232D  
Suggested retail price: 13.00 €\*

---

### **Carbide Tipped Anvil Series 511**



Range 55mm, 70mm (120mm)  
Art No. 21DZA232E  
Suggested retail price: 13.00 €\*

---

### **Carbide Tipped Anvil Series 511**



Range 60mm, 75mm (125mm)  
Art No. 21DZA232F  
Suggested retail price: 13.00 €\*

---

### **Carbide Tipped Anvil Series 511**



Range 80mm (130mm)  
Art No. 21DZA232G  
Suggested retail price: 15.00 €\*

---

### **Carbide Tipped Anvil Series 511**



Range 85mm (135mm)  
Art No. 21DZA232H  
Suggested retail price: 15.00 €\*

---



### **Carbide Tipped Anvil Series 511**

Range 90mm (140mm)  
Art No. 21DZA232J  
Suggested retail price: 16.00 €\*  

---



### **Carbide Tipped Anvil Series 511**

Range 95mm (145mm)  
Art No. 21DZA232L  
Suggested retail price: 16.00 €\*  

---



### **Carbide Tipped Anvil Series 511**

Range 100mm (150mm)  
Art No. 21DZA232M  
Suggested retail price: 16.00 €\*  

---



### **Washer Series 511**

0,5mm, Range 35-160mm  
Art No. 205457  
Suggested retail price: 7.00 €\*  

---



### **Washer Series 511**

1 mm, Range 35-160mm  
Art No. 205458  
Suggested retail price: 7.00 €\*  

---



### Washer Series 511

2 mm, Range 35-160mm  
Art No. 205459  
Suggested retail price: 7.00 €\*  


---



### Washer Series 511

3 mm, Range 35-160mm  
Art No. 205460  
Suggested retail price: 7.00 €\*  

---



### Sub-Anvil Series 511

50 mm  
Art No. 102178  
Suggested retail price: 24.00 €\*  

---