

2-Point Inside Measuring Instrument

Item number: 511-791-20

Images



Description

This is a compact and lightweight bore gauge due to the short length below the grip. It offers you the following benefits:

- A long plunger stroke gives you amazing accuracy.
- Contact points are carbide giving you high durability and wear resistance.
- A large grip reduces heat transfer from the operator by 50%.


Features

Inch-Metric:	Inch
Range:	0.7 - 1.4 "
Graduation:	0.0001"
Stroke of contact point:	18 - 60 mm: 1.2 mm 50 - 160 mm: 1.6 mm
Measuring depth:	2"
No. Dial Indicator:	2923AB-10
Number of anvils:	9
Accuracy:	2 μ m
Repeatability:	0.5 μ m
Digital/Analog:	Analog
Delivered:	In a box with bore gauge 511-781, dial indicator 2923AB-10, plastic cover for indicator 21DZA000, 9 anvils, 2 interchangeable washer, spanner 1202148

Mass:

320 g

Dimensions



Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



Digital Indicator, Bore Gauge ID-C

ASME/ANSI Type, Inch/Metric, 0,5", 0,00005", Flat Back Plate

Art No. 543-312B-10

Suggested retail price: 563.00 €*

Standard accessories:



2-Point Inside Measuring Instrument

Bore Gauge for Short Length, 0,7-1,4", w/o Indicator

Art No. 511-781

Suggested retail price: 258.00 €*



Dial Gauge, Flat Back, ANSI/AGD Type

Jewelled Bearing, Shockproof, 0,05", 0,0001"
Art No. 2923AB-10
Suggested retail price: 145.00 €*




Protector for Indicator (plastic cover)

Art No. 21DZA000
Suggested retail price: 20.00 €*



Carbide Tipped Anvil Series 511

Range 18 mm
Art No. 21DZA213A
Suggested retail price: 11.00 €*



Carbide Tipped Anvil Series 511

Range 20 mm
Art No. 21DZA213B
Suggested retail price: 11.00 €*




Carbide Tipped Anvil Series 511

Range 22 mm
Art No. 21DZA213C
Suggested retail price: 11.00 €*




Carbide Tipped Anvil Series 511

Range 24 mm
Art No. 21DZA213D
Suggested retail price: 12.00 €*




Carbide Tipped Anvil Series 511

Range 26 mm
Art No. 21DZA213E
Suggested retail price: 12.00 €*



Carbide Tipped Anvil Series 511

Range 28 mm
Art No. 21DZA213F
Suggested retail price: 12.00 €*



Carbide Tipped Anvil Series 511

Range 30 mm
Art No. 21DZA213G
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 32 mm
Art No. 21DZA213H
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 34 mm
Art No. 21DZA213J
Suggested retail price: 13.00 €*



Washer Series 511

0,5mm, Range 18-35mm
Art No. 205623
Suggested retail price: 7.00 €*



Washer Series 511

1mm, Range 18-35mm
Art No. 205624
Suggested retail price: 7.00 €*



Spanner/526

Art No. 102148
Price on application
