

2-Point Inside Measuring Instrument

Item number: 511-932-20

Images



Description

This is a wide range application set of Bore Gauges that automatically self-centres via a centring bridge and offers you the following benefits:

- Carbide for the contact point ensuring high durability and wear resistance
- It reduces the influence of heat from the operator's hand by 50% by making the grip hollow structured, thereby retaining high accuracy measurement.

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Range:	0.7 - 6 "
No. Dial Indicator:	2923AB-10
Stroke of contact point:	0.7 - 2.5 ": 0.047 " 2 - 16 ": 0.063 "
Graduation:	0.0001 "

Accuracy:	0.00008 "
Repeatability:	0.00002 "
Measuring depth:	4 " / 6 "
Measuring force:	≤5 N
Number of anvils:	26
Sub anvils:	1
Delivered:	In a box with bore gauge 511-731 / 511-732 / 511-733, dial indicator 2923AB-10, plastic cover for indicator 21DZA000, 26 anvils, 10 washers, 1 sub-anvil, spanner 102148
Mass:	810 g

Accessories

Optional accessories:



Digital Indicator, Bore Gauge ID-C

ASME/ANSI Type, Inch/Metric, 0,5", 0,00005",
Flat Back Plate
Art No. 543-312B-10
Suggested retail price: 563.00 €*



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application



Extension Rod Serie 511

125mm, 9mm Rod Diameter
Art No. 953549
Suggested retail price: 224.00 €*

Extension Rod Serie 511

250mm, 9mm Rod Diameter
Art No. 953550
Suggested retail price: 255.00 €*


Extension Rod Serie 511

500mm, 9mm Rod Diameter
Art No. 953551
Suggested retail price: 400.00 €*


Extension Rod Serie 511

125mm, 12mm Rod Diameter
Art No. 953552
Suggested retail price: 240.00 €*


Extension Rod Serie 511

250mm, 12mm Rod Diameter
Art No. 953553
Suggested retail price: 271.00 €*


Extension Rod Serie 511

500mm, 12mm Rod Diameter
Art No. 953554
Suggested retail price: 479.00 €*


Extension Rod Serie 511

750mm, 12mm Rod Diameter

Art No. 953555

Suggested retail price: 645.00 €*


Extension Rod Serie 511

1000mm, 12mm Rod Diameter

Art No. 953556

Suggested retail price: 870.00 €*


Standard accessories:

Dial Gauge, Flat Back, ANSI/AGD Type

Jewelled Bearing, Shockproof, 0,05", 0,0001"

Art No. 2923AB-10

Suggested retail price: 145.00 €*



2-Point Inside Measuring Instrument

Bore Gauge, 0,7-1,4", w/o Indicator

Art No. 511-731

Suggested retail price: 290.00 €*


2-Point Inside Measuring Instrument

Bore Gauge, 1,4-2,5", w/o Indicator

Art No. 511-732

Suggested retail price: 297.00 €*




2-Point Inside Measuring Instrument

Bore Gauge, 2-6", w/o Indicator
Art No. 511-733
Suggested retail price: 310.00 €*



Protector for Indicator (plastic cover)

Art No. 21DZA000
Suggested retail price: 14.50 €*



Carbide Tipped Anvil Series 511

Range 18 mm
Art No. 21DZA213A
Suggested retail price: 5.80 €*



Carbide Tipped Anvil Series 511

Range 20 mm
Art No. 21DZA213B
Suggested retail price: 6.50 €*



Carbide Tipped Anvil Series 511

Range 22 mm
Art No. 21DZA213C
Suggested retail price: 6.50 €*




Carbide Tipped Anvil Series 511

Range 24 mm
Art No. 21DZA213D
Suggested retail price: 8.30 €*



Carbide Tipped Anvil Series 511

Range 26 mm
Art No. 21DZA213E
Suggested retail price: 8.30 €*



Carbide Tipped Anvil Series 511

Range 28 mm
Art No. 21DZA213F
Suggested retail price: 8.30 €*



Carbide Tipped Anvil Series 511

Range 30 mm
Art No. 21DZA213G
Suggested retail price: 9.00 €*



Carbide Tipped Anvil Series 511

Range 32 mm
Art No. 21DZA213H
Suggested retail price: 9.00 €*



Carbide Tipped Anvil Series 511

Range 34 mm
Art No. 21DZA213J
Suggested retail price: 9.00 €*



Spanner/526

Art No. 102148
Price on application



Washer Series 511

0,5mm, Range 18-35mm
Art No. 205623
Suggested retail price: 4.20 €*



Washer Series 511

1mm, Range 18-35mm
Art No. 205624
Suggested retail price: 4.20 €*



Carbide Tipped Anvil Series 511

Range 50mm (100mm)
Art No. 21DZA232A
Suggested retail price: 8.00 €*



Carbide Tipped Anvil Series 511

Range 40mm, 55mm (105mm)
Art No. 21DZA232B
Suggested retail price: 8.50 €*



Carbide Tipped Anvil Series 511

Range 45mm, 60mm (110mm)
Art No. 21DZA232C
Suggested retail price: 9.00 €*



Carbide Tipped Anvil Series 511

Range 50mm, 65mm (115mm)
Art No. 21DZA232D
Suggested retail price: 9.50 €*



Carbide Tipped Anvil Series 511

Range 55mm, 70mm (120mm)
Art No. 21DZA232E
Suggested retail price: 9.80 €*



Carbide Tipped Anvil Series 511

Range 60mm, 75mm (125mm)
Art No. 21DZA232F
Suggested retail price: 10.30 €*



Carbide Tipped Anvil Series 511

Range 80mm (130mm)
Art No. 21DZA232G
Suggested retail price: 11.50 €*



Carbide Tipped Anvil Series 511

Range 85mm (135mm)
Art No. 21DZA232H
Suggested retail price: 11.80 €*



Carbide Tipped Anvil Series 511

Range 90mm (140mm)
Art No. 21DZA232J
Suggested retail price: 12.00 €*



Carbide Tipped Anvil Series 511

Range 95mm (145mm)
Art No. 21DZA232L
Suggested retail price: 12.30 €*



Carbide Tipped Anvil Series 511

Range 100mm (150mm)
Art No. 21DZA232M
Suggested retail price: 13.30 €*



Sub-Anvil Series 511

50 mm
Art No. 102178
Suggested retail price: 23.80 €*



Washer Series 511

0,5mm, Range 35-160mm
Art No. 205457
Suggested retail price: 4.20 €*



Washer Series 511

1 mm, Range 35-160mm
Art No. 205458
Suggested retail price: 4.20 €*



Washer Series 511

2 mm, Range 35-160mm
Art No. 205459
Suggested retail price: 4.20 €*



Washer Series 511

3 mm, Range 35-160mm
Art No. 205460
Suggested retail price: 4.20 €*
