

Digital Height Master

Item number: 515-374

Images



Description

This is a standard model with a digital display, that offers you the following benefits:

- It gives you all the essential specifications required for a versatile height standard.
- You can use it to calibrate and set height gauges and other measuring instruments.
- Models have two measuring faces on the same level, one facing up and the other down.
- It is supplied in a fitted wooden case


Features

Inch-Metric:	Metric
Range:	10 - 310 mm
Graduation:	0.002 mm
Power supply:	2 batteries SR-44
Digital step:	0,001 mm
Block step:	20 mm staggered
Feed error:	±2 μm
Retrace error:	2 μm
Micrometer adjustment:	20 mm

Micrometer feed:	0.5 mm
Block pitch accuracy:	Range \leq 310 mm : $\pm 1.5 \mu\text{m}$ 310 < range \leq 450 mm: $\pm 2.5 \mu\text{m}$ 450 < range \leq 610 mm: $\pm 3.5 \mu\text{m}$
Parallelism of blocks:	Range \leq 310mm: 2 μm 310 < range \leq 610mm: 2.5 μm
Battery life:	Approx. 1,8 years
DATA (output with cable) / HOLD (display value):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Data output:	Yes
PRESET:	Yes
ABS / INC (INC ZERO):	Yes
Delivered:	In a wooden case with certificate of inspection, 11 mm gauge block, 1 SR44 battery
Mass:	9.5 kg

Accessories

Optional accessories:



Auxiliary Block Kit for Bore Gauge

for 515-374/515-376/515-378
Art No. 515-111
Suggested retail price: 222.00 €*



Digimatic Cable, Straight, Data Button,

1 m
Art No. 959149
Suggested retail price: 48.00 €*



Digimatic Cable, Straight, Data Button

2 m
Art No. 959150
Suggested retail price: 57.00 €*
*including 20% VAT

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Straight,
with Data Button
Art No. 06AFM380C
Promo price: **98.00 €*
Suggested retail price: 124.00 €*
*including 20% VAT**

Promotion!



U-WAVE-T, Buzzer Type

Wireless Transmitter
Art No. 02AZD880G
Promo price: **129.00 €*
Suggested retail price: 187.00 €*
*including 20% VAT**

Promotion!



U-WAVE-T, IP67 Type

Wireless Transmitter
Art No. 02AZD730G
Promo price: **129.00 €*
Suggested retail price: 187.00 €*
*including 20% VAT**

Promotion!



Connection Cable C for U- WAVE

Straight, with Data Button
Art No. 02AZD790C
Promo price: **72.00 €*
Suggested retail price: 105.00 €*
*including 20% VAT**

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
