


## Digital Universal Protractor

Item number: 187-552

### Images



### Description

A Mitutoyo digital universal protractor for precise reading of angles on workpiece features, or setting angles on machine tools. Hardened stainless steel construction. Digimatic data output.

### Features

<b>Model:</b>	BP-D300E
<b>Inch-Metric:</b>	Inch/Metric
<b>Power supply:</b>	1 battery CR-2032
<b>Digital step:</b>	1' (0.01°)
<b>Blade length:</b>	12"
<b>Max. permissible error:</b>	2' (0.03°)
<b>Repeatability:</b>	1' (0.01°)
<b>Battery life:</b>	Approx. 2000 hours
<b>ON/OFF:</b>	Yes
<b>DATA (output with cable) / HOLD (display value):</b>	Yes
<b>Data output:</b>	Yes
<b>ZERO SET:</b>	Yes
<b>PRESET:</b>	Yes
<b>Angle sexagesimal/decimal:</b>	Yes
<b>Delivered:</b>	In a box including CR-2032 battery, 300 mm steel rule, holder for height gauge
<b>Display:</b>	LCD with character height 6.5 mm
<b>Mass:</b>	662 g

### Accessories

Optional accessories:



### Digimatic Cable, Flat Straight Type

1 m  
Art No. 905338  
Suggested retail price: 37.00 €\*  
~~37.00 €\*~~



### Digimatic Cable, Flat Straight Type

2 m  
Art No. 905409  
Suggested retail price: 44.00 €\*  
~~44.00 €\*~~

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Flat Straight Type  
Art No. 06AFM380F  
Promo price: **98.00 €\***  
Suggested retail price: ~~124.00 €\* 124.00 €\*~~

Promotion!



### U-WAVE-T, Buzzer Type

Wireless Transmitter  
Art No. 02AZD880G  
Promo price: **129.00 €\***  
Suggested retail price: ~~187.00 €\* 187.00 €\*~~

Promotion!



### U-WAVE-T, IP67 Type

Wireless Transmitter  
Art No. 02AZD730G  
Promo price: **129.00 €\***  
Suggested retail price: ~~187.00 €\* 187.00 €\*~~

Promotion!



## Connection Cable F for U-WAVE

Straight, without Data Button

Art No. 02AZD790F

Promo price: **68.00 €\***

Suggested retail price: ~~98.00 €\*~~

## Acute angle attachment

for Series 187

Art No. 187-105

Suggested retail price: **76.00 €\***



### Standard accessories:

## Steel Rule

**300mm/12"**, Metric/Inch

Art No. 187-107

Suggested retail price: **49.00 €\***




## Holder for Mounting on Height Gauges

Metric, Series 187

Art No. 950750

Suggested retail price: **43.00 €\***



### Spare parts

#### Consumable spares:



## Lithium battery CR-2032

1 pcs.

Art No. 05SAA217D

Suggested retail price: 10.00 €\*  

---