

Digital Micrometer IP65 Set

Item number: 293-961-30

Images



Dust- and
Water-
Protected

www.tuv.com
ID 0000040191



Description

This IP65 Micrometer offers outstanding accuracy, with data output, is highly robust and offers the following benefits:

- Oil-resistant material used for all plastic parts
- Extraordinary battery life of 2,4 years
- Excellent resistance against water and dust enables this micrometer to be used in machining situations that include splashing coolant fluid.

Features

Digital step:	0,001 mm
Delivered:	Including box, spanner, SR44 battery, setting standards (3 pcs.), certificate of inspection (2 pcs.)
Display:	LCD, character height 7.5 mm
Measuring face:	Carbide-tipped, micro-lap finish
Measuring spindle:	With spindle lock, \varnothing 6,35 mm, spindle pitch 0,5 mm
Scale:	Thimble and sleeve satin chrome finish
Data output:	Yes
Measuring force:	5 - 10 N
Power supply:	1 battery SR-44

Battery life:	Approx. 2,4 years
ABS / INC (INC ZERO):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Function lock:	Yes
HOLD:	Yes

Accessories

Optional accessories:



Digimatic Cable with Data Button IP Type

1 m, Micrometer Type
 Art No. 05CZA662
 Suggested retail price: 105.00 €*



Digimatic Cable with Data Button IP Type

2 m, Micrometer Type
 Art No. 05CZA663
 Suggested retail price: 107.00 €*

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type
 Art No. 06AFM380B
Promo price: 111.00 €*
 Suggested retail price: 141.00 €*

Promotion!



U-WAVE fit, Buzzer Type

Wireless Transmitter for Micrometer/Indicator
 Art No. 264-623
Promo price: 129.00 €*
 Suggested retail price: 185.00 €*

Promotion!



U-WAVE fit, IP67 Type

Wireless Transmitter for
Micrometer/Indicator
Art No. 264-622

Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for
Micrometer/Indicator
Art No. 264-626

Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for
Micrometer/Indicator
Art No. 264-627

Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



Connection Unit for IP Caliper, Micrometer

with Data Button for U-WAVE fit, U-WAVE fit
Bluetooth
Art No. 02AZF310

Promo price: **76.00 €***
Suggested retail price: ~~110.00 €*~~

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
