

Digital Screw Thread Micrometer IP65

Item number: 326-251-30

Images



Dust- and
Water-
Protected

www.tuv.com
ID 0000040191



Description

This Digimatic Screw Thread Micrometer should be used with optional, interchangeable, anvils/spindle-tips that allow you to measure a wide range of metric/unified and Whitworth screw-thread pitch diameters.


A metric (unified) 60° setting standard is included with all models except those measuring range from 0-25 mm.

Features

Digital/Analog:	Digital
Inch-Metric:	Metric
Range:	0 - 25 mm
Digital step:	0,001 mm
Delivered:	Including box, spanner, 1 SR44 battery, without interchangeable tips
Spindle feed error:	3 µm
Display:	LCD, character height 7.5 mm
Measuring face:	Interchangeable anvil/spindle inserts (optional)
Measuring spindle:	With spindle lock, ø6,35 mm, spindle pitch 0,5 mm

Scale:	Thimble and sleeve satin chrome finish, ø18 mm
Data output:	Yes
Measuring force:	5 - 10 N
Power supply:	1 battery SR-44
Battery life:	Approx. 2.4 years
ABS / INC (INC ZERO):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Function lock:	Yes
HOLD:	Yes
2 x PRESET:	Yes
Mass:	350 g

Dimensions



A: 39.5 mm

B: 25 mm

Accessories

Optional accessories:



Micrometer Stand, 45° Angle Type

for Micrometer 0-50mm/0-2"
 Art No. 156-105-10
 Suggested retail price: 58.00 €*

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"
 Art No. 156-101-10
 Promo price: **56.00 €***
 Suggested retail price: 70.00 €*

Interchangeable Tips

0,4-0,5mm/64-48TPI
Art No. 126-801
Suggested retail price: 77.00 €*



Interchangeable Tips

0,6-0,9mm/44-28TPI
Art No. 126-802
Suggested retail price: 77.00 €*



Interchangeable Tips

1-1,75mm/24-14TPI
Art No. 126-803
Suggested retail price: 77.00 €*



Interchangeable Tips

2-3mm/13-9TPI
Art No. 126-804
Suggested retail price: 77.00 €*



Interchangeable Tips

3,5-5mm/8-5TPI
Art No. 126-805
Suggested retail price: 77.00 €*



Interchangeable Tips

5,5-7mm/4,5-3,5TPI

Art No. 126-806

Suggested retail price: 77.00 €*



Interchangeable Tips

60-48 TPI

Art No. 126-811

Suggested retail price: 77.00 €*



Interchangeable Tips

48-40 TPI

Art No. 126-812

Suggested retail price: 77.00 €*



Interchangeable Tips

40-32 TPI

Art No. 126-813

Suggested retail price: 77.00 €*



Interchangeable Tips

32-24 TPI

Art No. 126-814

Suggested retail price: 77.00 €*



Interchangeable Tips

24-18 TPI

Art No. 126-815

Suggested retail price: 77.00 €*


Interchangeable Tips

18-14 TPI

Art No. 126-816

Suggested retail price: 77.00 €*


Interchangeable Tips

14-10 TPI

Art No. 126-817

Suggested retail price: 77.00 €*


Interchangeable Tips

10-7 TPI


Art No. 126-818

Suggested retail price: 77.00 €*


Interchangeable Tips

7-4,5 TPI

Art No. 126-819

Suggested retail price: 77.00 €*




Interchangeable Tips

7-5-3,5 TPI
Art No. 126-820
Suggested retail price: 77.00 €*



Interchangeable Tip Set (Metric/UNF)

6 pairs
Art No. 126-800
Suggested retail price: 414.00 €*



Interchangeable Tip Set (Whitworth)

10 pairs
Art No. 126-810
Suggested retail price: 674.00 €*

Promotion!



Connection Unit for IP Caliper, Micrometer

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth
Art No. 02AZF310
Promo price: 76.00 €*
Suggested retail price: 110.00 €*

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type
Art No. 06AFM380B
Promo price: 111.00 €*
Suggested retail price: 141.00 €*



Digimatic Cable with Data Button IP Type

1 m, Micrometer Type
Art No. 05CZA662
Suggested retail price: 105.00 €*
Suggested retail price: 105.00 €*
Suggested retail price: 105.00 €*



Digimatic Cable with Data Button IP Type

2 m, Micrometer Type
Art No. 05CZA663
Suggested retail price: 107.00 €*
Suggested retail price: 107.00 €*

Promotion!



U-WAVE fit, IP67 Type

Wireless Transmitter for
Micrometer/Indicator
Art No. 264-622
Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit, Buzzer Type

Wireless Transmitter for
Micrometer/Indicator
Art No. 264-623
Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for
Micrometer/Indicator
Art No. 264-626
Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for
Micrometer/Indicator
Art No. 264-627

Promo price: **129.00 €***
~~Suggested retail price: 185.00 €*~~

Promotion!

Mitutoyo

MiCAT

the standard in world
metrology software
MeasurLink™

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)

Art No. 06AGR543

Promo price: **268.00 €***
~~Suggested retail price: 340.00 €*~~



Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882
Suggested retail price: 7.00 €*