

## Digital Screw Thread Micrometer IP65

Item number: 326-353-30

### Images



### Description

This Digimatic Screw Thread Micrometer should be used with optional, interchangeable, anvils/spindle-tips that allow you to measure a wide range of metric/unified and Whitworth screw-thread pitch diameters.


A metric (unified) 60° setting standard is included with all models except those measuring range from 0-25 mm.

### Features

<b>Digital/Analog:</b>	Digital
<b>Inch-Metric:</b>	Inch/Metric
<b>Range:</b>	2 - 3 "
<b>Digital step:</b>	0.00005"/0.001 mm
<b>Delivered:</b>	Including box, spanner, setting standard, 1 SR44 battery, without interchangeable tips

<b>Spindle feed error:</b>	0.00015 inch
<b>Display:</b>	LCD, character height 7.5 mm
<b>Measuring face:</b>	Interchangeable anvil/spindle inserts (optional)
<b>Measuring spindle:</b>	With spindle lock, $\varnothing 6,35$ mm, spindle pitch 0,5 mm
<b>Scale:</b>	Thimble and sleeve satin chrome finish, $\varnothing 18$ mm
<b>Data output:</b>	Yes
<b>Measuring force:</b>	5 - 10 N
<b>Power supply:</b>	1 battery SR-44
<b>Battery life:</b>	Approx. 2.4 years
<b>ABS / INC (INC ZERO):</b>	Yes
<b>Auto Power OFF after 20 min. non use:</b>	Yes
<b>Low voltage alarm:</b>	Yes
<b>Function lock:</b>	Yes
<b>HOLD:</b>	Yes
<b>2 x PRESET:</b>	Yes
<b>Mass:</b>	470 g

## Dimensions



**A:** 90 mm

**B:** 45 mm

## Accessories

### Optional accessories:

Promotion!

Mitutoyo

MiCAT

the standard in world metrology software


measurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Promo price: 268.00 €\*  
Suggested retail price: 340.00 €\*



USB-ITPAK



### Digimatic Cable with Data Button IP Type

1 m, Micrometer Type  
Art No. 05CZA662  
Suggested retail price: 105.00 €\*  

---



### Digimatic Cable with Data Button IP Type

2 m, Micrometer Type  
Art No. 05CZA663  
Suggested retail price: 107.00 €\*  

---

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type  
Art No. 06AFM380B  
Promo price: **111.00 €\***   
Suggested retail price: ~~141.00 €\*~~

Promotion!



### U-WAVE fit, IP67 Type

Wireless Transmitter for Micrometer/Indicator  
Art No. 264-622  
Promo price: **129.00 €\***   
Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit, Buzzer Type

Wireless Transmitter for Micrometer/Indicator  
Art No. 264-623  
Promo price: **129.00 €\***   
Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for Micrometer/Indicator  
Art No. 264-626

Promo price: **129.00 €\***  
Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for Micrometer/Indicator  
Art No. 264-627

Promo price: **129.00 €\***  
Suggested retail price: ~~185.00 €\*~~

Promotion!



### Connection Unit for IP Caliper, Micrometer

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth  
Art No. 02AZF310

Promo price: **76.00 €\***  
Suggested retail price: ~~110.00 €\*~~

Promotion!



### Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"  
Art No. 156-101-10

Promo price: **56.00 €\***  
Suggested retail price: ~~70.00 €\*~~

### Interchangeable Tips

0,4-0,5mm/64-48TPI  
Art No. 126-801  
Suggested retail price: ~~77.00 €\*~~



### Interchangeable Tips

0,6-0,9mm/44-28TPI  
Art No. 126-802  
Suggested retail price: 77.00 €\*  

---



### Interchangeable Tips

1-1,75mm/24-14TPI  
Art No. 126-803  
Suggested retail price: 77.00 €\*  

---



### Interchangeable Tips

2-3mm/13-9TPI  
Art No. 126-804  
Suggested retail price: 77.00 €\*  

---



### Interchangeable Tips

3,5-5mm/8-5TPI  
Art No. 126-805  
Suggested retail price: 77.00 €\*  

---




### Interchangeable Tips

5,5-7mm/4,5-3,5TPI  
Art No. 126-806  
Suggested retail price: 77.00 €\*  



---





## Interchangeable Tips

60-48 TPI  
Art No. 126-811  
Suggested retail price: 77.00 €\*  




## Interchangeable Tips

48-40 TPI  
Art No. 126-812  
Suggested retail price: 77.00 €\*  
  




## Interchangeable Tips

40-32 TPI  
Art No. 126-813  
Suggested retail price: 77.00 €\*  
  


## Interchangeable Tips

32-24 TPI  
Art No. 126-814  
Suggested retail price: 77.00 €\*  
  


## Interchangeable Tips

24-18 TPI  
Art No. 126-815  
Suggested retail price: 77.00 €\*  
  




### Interchangeable Tips

18-14 TPI  
Art No. 126-816  
Suggested retail price: 77.00 €\*  

---



### Interchangeable Tips

14-10 TPI  
Art No. 126-817  
Suggested retail price: 77.00 €\*  

---



### Interchangeable Tips

10-7 TPI  
Art No. 126-818  
Suggested retail price: 77.00 €\*  

---



### Interchangeable Tips

7-4,5 TPI  
Art No. 126-819  
Suggested retail price: 77.00 €\*  

---



### Interchangeable Tips

7-5-3,5 TPI  
Art No. 126-820  
Suggested retail price: 77.00 €\*  

---



## Interchangeable Tip Set (Metric/UNF)

6 pairs

Art No. 126-800

Suggested retail price: 414.00 €\*



## Interchangeable Tip Set (Whitworth)

10 pairs

Art No. 126-810

Suggested retail price: 674.00 €\*



## Setting Standard Screw Thread Micrometer

55°, Length: 2"

Art No. 167-284

Suggested retail price: 74.00 €\*

Standard accessories:



## Setting Standard Screw Thread Micrometer

60°, Length: 2"

Art No. 167-295

Suggested retail price: 74.00 €\*

### Spare parts

Consumable spares:



## Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €\*  

---