

## Digital Micrometer Interchangeable Anvil

Item number: 340-525

### Images



### Description

This Digimatic Micrometer offers you an extra wide measuring range, and has the following benefits:

- Easy, interchangeable anvils allow a wide range of measurements.
- Ratchet stop for constant force.

### Features

<b>Digital/Analog:</b>	Digital
<b>Delivered:</b>	Including box, spanner, setting standard, 4 anvils, 2 SR44 batteries
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	800 - 900 mm
<b>Digital step:</b>	0,001 mm
<b>Limit of error:</b>	$\pm 16 \mu\text{m}$
<b>Spindle feed error:</b>	$3 \mu\text{m}$
<b>Flatness:</b>	$1 \mu\text{m}$
<b>Parallelism:</b>	$11 \mu\text{m}$
<b>Display:</b>	LCD, character height 7.5 mm



Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Straight,  
with Data Button  
Art No. 06AFM380C

Promo price: **98.90 €\***

Suggested retail price: ~~124.00 €\*~~



### Digimatic Cable, Straight, Data Button,

1m

Art No. 959149

Suggested retail price: 48.00 €\*



### Digimatic Cable, Straight, Data Button

2m

Art No. 959150

Suggested retail price: 57.00 €\*



### Digimatic Cable with Data Button

1m, Flat L-Shape Left Type

Art No. 04AZB512

Suggested retail price: 95.00 €\*



### Digimatic Cable, Straight, Data Button

2m, Flat L-Shape Left Type

Art No. 04AZB513

Suggested retail price: 106.00 €\*

Promotion!



### U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: **129.00 €\***

Suggested retail price: ~~187.00 €\*~~

Promotion!



### U-WAVE-T, Buzzer Type

Wireless Transmitter

Art No. 02AZD880G

Promo price: **129.00 €\***

Suggested retail price: ~~187.00 €\*~~

Promotion!

Mitutoyo

MiCAT

the standard in world  
metrology software  
measurLink®

### USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available  
Online)

Art No. 06AGR543

Promo price: **259.00 €\***

Suggested retail price: ~~340.00 €\*~~



Standard accessories:

### Micrometer Setting Standard

Length: 800mm

Art No. 167-132

Suggested retail price: **312.00 €\***



### Micrometer Setting Standard


Length: 825mm

Art No. 167-133


Suggested retail price: **324.00 €\***



## Micrometer Setting Standard

Length: 850mm  
Art No. 167-134  
Suggested retail price: 350.00 €\*  


## Micrometer Setting Standard

Length: 875mm  
Art No. 167-135  
Suggested retail price: 355.00 €\*  


### Spare parts

#### Consumable spares:



## Battery SR44 1,5 V

Art No. 938882  
Suggested retail price: 10.00 €\*  

---