


## Digital Inside Microm. Caliper Type

Item number: 345-350-30

### Images



### Description

The Digimatic Caliper Jaw Inside Micrometer offers you the following benefits:


- Carbide measuring faces
- A setting standard (optional) is needed to accurately set the micrometer to the reference point.

### Features

<b>Inch-Metric:</b>	Inch/Metric
<b>Digital/Analog:</b>	Digital
<b>Range:</b>	0.2 - 1.2 "
<b>Digital step:</b>	0.00005"/0.001 mm
<b>Measuring force:</b>	1-6 N
<b>Power supply:</b>	1 battery SR-44
<b>Scale:</b>	Thimble and sleeve satin chrome finish, $\varnothing$ 18 mm
<b>Battery life:</b>	2,4 years
<b>Display:</b>	LCD, character height 7.5 mm
<b>Measuring spindle:</b>	With spindle lock, spindle pitch 0,635 mm
<b>Measuring face:</b>	Carbide tipped
<b>DATA/HOLD:</b>	Yes
<b>Auto Power OFF after 20 min. non use:</b>	Yes

<b>Low voltage alarm:</b>	Yes
<b>Function lock:</b>	Yes
<b>2 x PRESET:</b>	Yes
<b>Delivered:</b>	Including box, spanner, 1 SR44 battery, without setting standard
<b>Data output:</b>	Yes
<b>Mass:</b>	305 g

## Dimensions



## Accessories

### Optional accessories:



### Digimatic Cable with Data Button IP Type

1 m, Micrometer Type  
 Art No. 05CZA662  
 Suggested retail price: 105.00 €\*



### Digimatic Cable with Data Button IP Type

2 m, Micrometer Type  
 Art No. 05CZA663  
 Suggested retail price: 107.00 €\*

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Flat Straight Type  
 Art No. 06AFM380F  
 Promo price: **98.00 €\***  
 Suggested retail price: ~~124.00 €\*~~

Promotion!



### U-WAVE fit, Buzzer Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-623

Promo price: **129.00 €\***  
Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit, IP67 Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-622

Promo price: **129.00 €\***  
Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-627

Promo price: **129.00 €\***  
Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-626

Promo price: **129.00 €\***  
Suggested retail price: ~~185.00 €\*~~

Promotion!



### Connection Unit for IP Caliper, Micrometer

with Data Button for U-WAVE fit, U-WAVE fit  
Bluetooth  
Art No. 02AZF310

Promo price: **76.00 €\***  
Suggested retail price: ~~110.00 €\*~~

Consumable spares:

---



**Battery SR44 1,5 V**

Art No. 938882

Suggested retail price: 7.00 €\*  

---