

# Digital Microm., Non Rotating Spindle

Item number: 406-353-30

## Images



## Description

This Micrometer features a non-rotating spindle, and offers the following benefits:

- Sliding spindle, not rotating.
- Ratchet stop.
- Data output.

## Features

|                                      |   |
|--------------------------------------|---|
| <b>Digital/Analog:</b>               | Digital   |
| <b>Inch-Metric:</b>                  | Inch/Metric                                       |
| <b>Range:</b>                        | 3 - 4 "   |
| <b>Digital step:</b>                 | 0.00005"/0.001 mm                                 |
| <b>Max. Permissible Error J MPE:</b> | ±0.0002"  |
| <b>Delivered:</b>                    | Including box, setting standard, 1 battery, key   |
| <b>Flatness:</b>                     | 0.000012"   |
| <b>Parallelism:</b>                  | 0.00016"  |
| <b>Display:</b>                      | LCD, character height 7.5 mm                      |
| <b>Measuring face:</b>               | Carbide-tipped, micro-lap finish                  |
| <b>Measuring spindle:</b>            | With spindle lock, ø6.35 mm, spindle pitch 0.5 mm |
| <b>Scale:</b>                        | Thimble and sleeve satin chrome finish, ø18 mm    |
| <b>Data output:</b>                  | Yes   |

|  |                   |
|--|-------------------|
| <b>Measuring force:</b>                      | 3 - 8 N           |
| <b>Power supply:</b>                         | 1 battery SR-44   |
| <b>Battery life:</b>                         | Approx. 2.4 years |
| <b>ORIGIN:</b>                               | Yes               |
| <b>ABS / INC (INC ZERO):</b>                 | Yes               |
| <b>Auto Power OFF after 20 min. non use:</b> | Yes               |
| <b>Low voltage alarm:</b>                    | Yes               |
| <b>Function lock:</b>                        | Yes               |
| <b>HOLD:</b>                                 | Yes               |
| <b>Mass:</b>                                 | 460 g             |

## Accessories

### Optional accessories:

**Promotion!**



**Micrometer Stand, Adjustable Angle Type**

for Micrometer 0-100mm/0-4"  
Art No. 156-101-10

Promo price: **56.00 €\***   
Suggested retail price: ~~70.00 €\*~~

**Promotion!**



**Connection Unit for IP Caliper, Micrometer**

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth  
Art No. 02AZF310

Promo price: **76.00 €\***   
Suggested retail price: ~~110.00 €\*~~

**Promotion!**



**USB Input Tool Direct (Digimatic to USB)**

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type  
Art No. 06AFM380B

Promo price: **111.00 €\***   
Suggested retail price: ~~141.00 €\*~~



### Digimatic Cable with Data Button IP Type

1 m, Micrometer Type  
Art No. 05CZA662  
Suggested retail price: 105.00 €\*  
Suggested retail price: 105.00 €\*  
Suggested retail price: 105.00 €\*



### Digimatic Cable with Data Button IP Type

2 m, Micrometer Type  
Art No. 05CZA663  
Suggested retail price: 107.00 €\*  
Suggested retail price: 107.00 €\*

Promotion!



### U-WAVE fit, IP67 Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-622  
Promo price: **129.00 €\***   
Suggested retail price: 185.00 €\*  
Suggested retail price: 185.00 €\*

Promotion!



### U-WAVE fit, Buzzer Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-623  
Promo price: **129.00 €\***   
Suggested retail price: 185.00 €\*  
Suggested retail price: 185.00 €\*

Promotion!



### U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-626  
Promo price: **129.00 €\***   
Suggested retail price: 185.00 €\*  
Suggested retail price: 185.00 €\*

Promotion!



## U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for  
Micrometer/Indicator  
Art No. 264-627

Promo price: **129.00 €\***   
Suggested retail price: ~~185.00 €\*~~

Promotion!

Mitutoyo

MiCAT

the standard in world  
metrology software  
MeasurLink®

## USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available  
Online)

Art No. 06AGR543

Promo price: **268.00 €\***   
Suggested retail price: ~~340.00 €\*~~



Standard accessories:

## Micrometer Setting Standard

Length: 3"  
Art No. 167-143  
Suggested retail price: **37.00 €\***



Spare parts

Consumable spares:



## Battery SR44 1,5 V

Art No. 938882  
Suggested retail price: **7.00 €\***

