

Digital 3-Point Internal Micrometer

Item number: 468-171

Images



Dust- and
Waterproof
IP65

www.tuv.com
ID 0000021605



Description

These are three-point internal micrometers that offer you the following benefits:


- Individual micrometer.
- Titanium-coated measuring pins give you excellent durability and impact resistance.
- They also have excellent resistance against water and dust (IP65 protection level), allowing you to use this product in machining situations that include splashing coolant fluid.
- Large LCD display with character height of 7,5 mm enables you to read measurements easily.

- Without setting rings or extensions.

Features

Model:	HTD-75R
Inch-Metric:	Metric
Digital/Analog:	Digital
Range:	62 - 75 mm
Digital step:	0,001 mm
Max. Permissible Error J MPE:	±4 µm
Power supply:	1 battery SR-44
Battery life:	Approx. 1.2 years
Display:	LCD, character height 7.5 mm
Measuring face:	Titanium-coated hardened steel taper: tungsten carbide
ABS / INC (INC ZERO):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Function lock:	Yes
HOLD:	Yes
2 x PRESET:	Yes
Delivered:	Including box, hex wrench, spanner, screwdriver, 1 SR44 battery, certificate of inspection
Data output:	Yes
Mass:	630 g

Dimensions



Accessories

Optional accessories:



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: 56.00 €*

Suggested retail price: 70.00 €*



Setting Ring 62mm

Steel
Art No. 177-314
Suggested retail price: 293.00 €*
~~Suggested retail price: 293.00 €*
Suggested retail price: 293.00 €*
Suggested retail price: 293.00 €*
Suggested retail price: 293.00 €*~~

Promotion!



Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type
Art No. 02AZD790B

Promo price: **76.00 €*
~~Suggested retail price: 110.00 €*
~~Suggested retail price: 110.00 €*
~~Suggested retail price: 110.00 €*
~~Suggested retail price: 110.00 €*~~~~~~~~**

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type
Art No. 06AFM380B

Promo price: **111.00 €*
~~Suggested retail price: 141.00 €*
~~Suggested retail price: 141.00 €*
~~Suggested retail price: 141.00 €*~~~~~~**



Digimatic Cable with Data Button IP Type

1 m, Micrometer Type
Art No. 05CZA662
Suggested retail price: 105.00 €*
~~Suggested retail price: 105.00 €*
~~Suggested retail price: 105.00 €*~~~~



Digimatic Cable with Data Button IP Type

2 m, Micrometer Type
Art No. 05CZA663
Suggested retail price: 107.00 €*
~~Suggested retail price: 107.00 €*
~~Suggested retail price: 107.00 €*~~~~

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
