

2-Point Inside Measuring Instrument

Item number: 511-211-20

Images



6 - 10mm

Description

These are bore gauges that automatically self-centre via a centring bridge.

They offer you the following benefits:

- A long plunger stroke gives you amazing accuracy.
- Interchangeable washers 0.5 mm thick are supplied as standard accessories, so you can enable setting in small steps.
- Contact points are carbide (>18 mm range), giving you high durability and wear resistance.
- A large grip reduces heat transfer from the operator by 50%.

Features


Inch-Metric:	Metric
Digital/Analog:	Analog
Range:	6 - 10 mm
Graduation:	0.01 mm
Stroke of contact point:	0.5 mm
Measuring depth:	50 mm
No. Dial Indicator:	2046AB
Number of anvils:	9
Accuracy:	5 μ m
Repeatability:	2 μ m
Measuring force:	\leq 2 N

Delivered:

In a box with bore gauge 511-209, dial indicator 2046AB, plastic cover for indicator 21DZA000, 9 anvils

Mass:

255 g

Dimensions**Accessories****Optional accessories:****Digital Indicator, Bore Gauge ID-C**

12,7mm, 0,001mm, Flat Back Plate
Art No. 543-310B-10
Suggested retail price: 563.00 €*

Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application

Standard accessories:**Anvil (6 mm)/511**

Small Holes Type, 6 mm/0,24 "
Art No. 952168
Price on application





Anvil (6.5mm)/511

Art No. 952169

Price on application



Anvil (7mm)/511

Art No. 952170

Price on application



Anvil (7.5mm)/511

Art No. 952414

Price on application



Anvil (8mm)/511

Art No. 952415

Price on application



Anvil (8.5mm)/511

Art No. 952416

Price on application

Anvil (9MM)/511

Art No. 952417

Price on application



Anvil (9.5mm)/511

Art No. 952418

Price on application



Anvil (10mm)/511

Art No. 952419

Price on application




206709

Spanner/511

Art No. 206709

Price on application



Tweezers/511

Art No. 206710

Price on application



Promotion!



Dial Gauge, Flat Back, ISO Type

10mm, 0,01mm

Art No. 2046AB

Promo price: **37.90 €***

Suggested retail price: ~~48.00 €*~~



2-Point Inside Measuring Instrument

Bore Gauge, 6-10mm, w/o Indicator

Art No. 511-209

Suggested retail price: **470.00 €***



Protector for Indicator (plastic cover)

Art No. 21DZA000

Suggested retail price: **20.00 €***