


## 2-Point Inside Measuring Instrument

Item number: 511-428-20

### Images



### Description


This is a bore gauge for measuring blind holes that offers you the following benefits:

- You can measure the inside diameter close to the bottom of blind holes.
- Contact points are carbide giving you high durability and wear resistance.

### Features

<b>Inch-Metric:</b>	Inch
<b>Digital/Analog:</b>	Analog
<b>Range:</b>	0.6 - 1.4 "
<b>Graduation:</b>	0.0005"
<b>Stroke of contact point:</b>	1.2 mm
<b>Measuring depth:</b>	6"
<b>No. Dial Indicator:</b>	2922AB
<b>Accuracy:</b>	4 μm
<b>Repeatability:</b>	1 μm
<b>Delivered:</b>	In a box with bore gauge 511-418, dial indicator 2922AB, plastic cover for indicator 21DZA000, 11 anvils, 1 interchangeable washer
<b>Mass:</b>	350 g

### Dimensions



Optional accessories:

### Extension Rod Serie 511

125mm, 9mm Rod Diameter  
Art No. 953549  
Suggested retail price: 230.00 €\*  

---



### Extension Rod Serie 511

250mm, 9mm Rod Diameter  
Art No. 953550  
Suggested retail price: 257.00 €\*  

---



### Extension Rod Serie 511

500mm, 9mm Rod Diameter  
Art No. 953551  
Suggested retail price: 399.00 €\*  

---



### Digital Indicator, Bore Gauge ID-C

ASME/ANSI Type, Inch/Metric, 0,5", 0,00005",  
Flat Back Plate  
Art No. 543-312B-10  
Suggested retail price: 563.00 €\*  

---





## Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application

Standard accessories:



## 2-Point Inside Measuring Instrument

Bore Gauge for Blind Holes, 0,6-1,4", w/o Indicator

Art No. 511-418

Suggested retail price: 419.00 €\*



## Dial Gauge, Flat Back, ANSI/AGD Type

0,125", 0,0005"

Art No. 2922AB

Suggested retail price: 107.00 €\*



## Protector for Indicator (plastic cover)

Art No. 21DZA000

Suggested retail price: 20.00 €\*

### ANVIL NO.1 FOR BORE GAGE

511-  
Art No. 21DZA376A  
Price on application



### ANVIL NO.2 FOR BORE GAGE

511-4xx  
Art No. 21DZA376B  
Price on application




### ANVIL NO.3 FOR BORE GAGE

511-4xx  
Art No. 21DZA376C  
Price on application



### ANVIL NO.4 FOR BORE GAGE

511-4xx  
Art No. 21DZA376D  
Price on application



### ANVIL NO.5 FOR BORE GAGE

511-4xx  
Art No. 21DZA376E  
Price on application





### ANVIL NO.6 FOR BORE GAGE

511-4xx  
Art No. 21DZA376F  
Price on application



### ANVIL NO.7 FOR BORE GAGE

511-4xx  
Art No. 21DZA376G  
Price on application



### ANVIL NO.8 FOR BORE GAGE

511-4xx  
Art No. 21DZA376H  
Price on application



### ANVIL NO.9 FOR BORE GAGE

511-4xx  
Art No. 21DZA376j  
Price on application




### ANVIL NO.10 FOR BORE GAG

E 511-4xx  
Art No. 21DZA376L  
Price on application

### **ANVIL NO.11 FOR BORE GAG**

E 511-4xx  
Art No. 21DZA376M  
**Price on application**



### **Washer 0.5mm/.02"/511**

Art No. 212127  
**Price on application**



### **SUB ANVIL FOR BORE GAGE**

Art No. 21DAA563  
**Price on application**



### **Spanner/511**

Art No. 204354  
**Price on application**

