


2-Point Inside Measuring Instrument

Item number: 511-429-20

Images



Description


This is a bore gauge for measuring blind holes that offers you the following benefits:

- You can measure the inside diameter close to the bottom of blind holes.
- Contact points are carbide giving you high durability and wear resistance.

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Stroke of contact point:	1.2 mm
Measuring depth:	6"
Accuracy:	4 μm
Repeatability:	1 μm
Delivered:	In a box with bore gauge 511-419, dial indicator 2922AB, plastic cover for indicator 21DZA000, 6 anvils, 4 interchangeable washer

Dimensions



Accessories

Optional accessories:

Extension Rod Serie 511

125mm, 9mm Rod Diameter
Art No. 953549
Suggested retail price: 230.00 €*



Extension Rod Serie 511

250mm, 9mm Rod Diameter
Art No. 953550
Suggested retail price: 257.00 €*



Extension Rod Serie 511

500mm, 9mm Rod Diameter
Art No. 953551
Suggested retail price: 399.00 €*



Digital Indicator, Bore Gauge ID-C

ASME/ANSI Type, Inch/Metric, 0,5", 0,00005",
Flat Back Plate
Art No. 543-312B-10
Suggested retail price: 563.00 €*

Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application





2-Point Inside Measuring Instrument

Bore Gauge for Blind Holes, 1,4-2,4", w/o Indicator

Art No. 511-419

Suggested retail price: 439.00 €*



Dial Gauge, Flat Back, ANSI/AGD Type

0,125", 0,0005"

Art No. 2922AB

Suggested retail price: 107.00 €*



Protector for Indicator (plastic cover)

Art No. 21DZA000

Suggested retail price: 20.00 €*



ANVIL NO.1 FOR BORE GAGE

511-4xx

Art No. 21DZA404A

Price on application



ANVIL NO.2 FOR BORE GAGE

511-4xx

Art No. 21DZA404B

Price on application



ANVIL NO.3 FOR BORE GAGE

511-4xx
Art No. 21DZA404C
[Price on application](#)



ANVIL NO.4 FOR BORE GAGE

511-4XX
Art No. 21DZA404D
[Price on application](#)



ANVIL NO.5 FOR BORE GAGE

511-4xx
Art No. 21DZA404E
[Price on application](#)



ANVIL NO.6 FOR BORE GAGE

511-4xx
Art No. 21DZA404F
[Price on application](#)



Washer 0.5mm/.02"/511

Art No. 212127
[Price on application](#)



Washer 1mm/.04"/511

Art No. 212128

Price on application



Washer 2mm/.08"/511

Art No. 212129

Price on application



Washer 3mm/.12"/511

Art No. 212130

Price on application



Spanner/511

Art No. 204354

Price on application