


2-Point Inside Measuring Instrument

Item number: 511-711-20

Images



Description

This is a short range application Bore Gauge Set that automatically self-centres via a centring bridge and offers you the following benefits:


- It reduces the influence of heat from the operator's hand by 50% by making the grip hollow structured, thereby retaining high accuracy measurement.
- Interchangeable washers (0,5 mm thick) are supplied as standard accessories, so you can enable setting in small steps.
- Contact points are carbide (>18 mm range), giving you high durability and wear resistance.

Features

Inch-Metric:	Metric
Range:	18 - 35 mm

Graduation:	0.01 mm
Stroke of contact point:	1.2 mm
Measuring depth:	100 mm
No. Dial Indicator:	2046AB
Number of anvils:	9
Accuracy:	2 µm
Repeatability:	0.5 µm
Digital/Analog:	Analog
Delivered:	In a box with bore gauge 511-701, dial indicator 2046AB, plastic cover for indicator 21DZA000, 9 anvils, 2 interchangeable washer, spanner 102148
Mass:	330 g

Dimensions



Accessories

Optional accessories:

Extension Rod Serie 511

125mm, 9mm Rod Diameter
 Art No. 953549
 Suggested retail price: 230.00 €*



Extension Rod Serie 511

250mm, 9mm Rod Diameter
 Art No. 953550
 Suggested retail price: 257.00 €*



Extension Rod Serie 511

500mm, 9mm Rod Diameter

Art No. 953551

Suggested retail price: 399.00 €*


Digital Indicator, Bore Gauge ID-C

12,7mm, 0,001mm, Flat Back Plate

Art No. 543-310B-10

Suggested retail price: 563.00 €*


Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195


Price on application


Standard accessories:

Carbide Tipped Anvil Series 511

Range 18 mm

Art No. 21DZA213A

Suggested retail price: 11.00 €*




Carbide Tipped Anvil Series 511

Range 20 mm
Art No. 21DZA213B
Suggested retail price: 11.00 €*




Carbide Tipped Anvil Series 511

Range 22 mm
Art No. 21DZA213C
Suggested retail price: 11.00 €*




Carbide Tipped Anvil Series 511

Range 24 mm
Art No. 21DZA213D
Suggested retail price: 12.00 €*




Carbide Tipped Anvil Series 511

Range 26 mm
Art No. 21DZA213E
Suggested retail price: 12.00 €*



Carbide Tipped Anvil Series 511

Range 28 mm
Art No. 21DZA213F
Suggested retail price: 12.00 €*



Carbide Tipped Anvil Series 511

Range 30 mm
Art No. 21DZA213G
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 32 mm
Art No. 21DZA213H
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 34 mm
Art No. 21DZA213J
Suggested retail price: 13.00 €*



Washer Series 511

0,5mm, Range 18-35mm
Art No. 205623
Suggested retail price: 7.00 €*



Washer Series 511

1mm, Range 18-35mm
Art No. 205624
Suggested retail price: 7.00 €*



Spanner/526

Art No. 102148

Price on application



2-Point Inside Measuring Instrument

Bore Gauge, 18-35mm, w/o Indicator

Art No. 511-701

Suggested retail price: 290.00 €*

Promotion!



Dial Gauge, Flat Back, ISO Type

10mm, 0,01mm

Art No. 2046AB

Promo price: 37.90 €*

Suggested retail price: 48.00 €*



Protector for Indicator (plastic cover)

Art No. 21DZA000

Suggested retail price: 20.00 €*