

## 2-Point Inside Measuring Instrument

Item number: 511-792-20

### Images



### Description

This is a compact and lightweight bore gauge due to the short length below the grip. It offers you the following benefits:

- A long plunger stroke gives you amazing accuracy.
- Contact points are carbide giving you high durability and wear resistance.
- A large grip reduces heat transfer from the operator by 50%.


### Features

<b>Inch-Metric:</b>	Inch
<b>Range:</b>	1.4 - 2.5 "
<b>Graduation:</b>	0.0001"
<b>Stroke of contact point:</b>	18 - 60 mm: 1.2 mm 50 - 160 mm: 1.6 mm
<b>Measuring depth:</b>	2"
<b>No. Dial Indicator:</b>	2923AB-10
<b>Number of anvils:</b>	6
<b>Accuracy:</b>	2 $\mu$ m
<b>Repeatability:</b>	0.5 $\mu$ m
<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a box with bore gauge 511-782, dial indicator 2923AB-10, plastic cover for indicator 21DZA000, 6 anvils, 4 interchangeable washer

Mass:

380 g

## Dimensions



## Accessories

### Optional accessories:



### Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



### Digital Indicator, Bore Gauge ID-C

ASME/ANSI Type, Inch/Metric, 0,5", 0,00005", Flat Back Plate

Art No. 543-312B-10

Suggested retail price: 563.00 €\*

### Standard accessories:



### 2-Point Inside Measuring Instrument

Bore Gauge for Short Length, 1,4-2,5", w/o Indicator

Art No. 511-782

Suggested retail price: 268.00 €\*



### Dial Gauge, Flat Back, ANSI/AGD Type

Jewelled Bearing, Shockproof, 0,05", 0,0001"  
Art No. 2923AB-10  
Suggested retail price: 145.00 €\*



### Protector for Indicator (plastic cover)

Art No. 21DZA000  
Suggested retail price: 20.00 €\*



### Carbide Tipped Anvil Series 511

Range 50mm (100mm)  
Art No. 21DZA232A  
Suggested retail price: 13.00 €\*



### Carbide Tipped Anvil Series 511

Range 40mm, 55mm (105mm)  
Art No. 21DZA232B  
Suggested retail price: 13.00 €\*



### Carbide Tipped Anvil Series 511

Range 45mm, 60mm (110mm)  
Art No. 21DZA232C  
Suggested retail price: 13.00 €\*

### **Carbide Tipped Anvil Series 511**



Range 50mm, 65mm (115mm)  
Art No. 21DZA232D  
Suggested retail price: 13.00 €\*  

---

### **Carbide Tipped Anvil Series 511**



Range 55mm, 70mm (120mm)  
Art No. 21DZA232E  
Suggested retail price: 13.00 €\*  

---

### **Carbide Tipped Anvil Series 511**



Range 60mm, 75mm (125mm)  
Art No. 21DZA232F  
Suggested retail price: 13.00 €\*  

---

### **Washer Series 511**



0,5mm, Range 35-160mm  
Art No. 205457  
Suggested retail price: 7.00 €\*  

---

### **Washer Series 511**



1 mm, Range 35-160mm  
Art No. 205458  
Suggested retail price: 7.00 €\*  

---



### Washer Series 511

2 mm, Range 35-160mm  
Art No. 205459  
Suggested retail price: 7.00 €\*



### Washer Series 511

3 mm, Range 35-160mm  
Art No. 205460  
Suggested retail price: 7.00 €\*