


2-Point Inside Measuring Instrument

Item number: 511-922-20

Images



Description

This is a wide range application set of Bore Gauges that automatically self-centres via a centring bridge and offers you the following benefits:

- Carbide for the contact point ensuring high durability and wear resistance
- It reduces the influence of heat from the operator's hand by 50% by making the grip hollow structured, thereby retaining high accuracy measurement.


Features

Inch-Metric:	Metric
Range:	18 - 150 mm
Graduation:	0.001 mm
Measuring depth:	100/150 mm
No. Dial Indicator:	2109AB-10
Accuracy:	2 μ m
Repeatability:	0.5 μ m
Digital/Analog:	Analog
Delivered:	In a box with bore gauge 511-701 / 511-702 / 511-703, dial indicator 2109AB-10, plastic cover for indicator 21DZA000, 26 anvils, 10 washers, 1 sub-anvil, spanner 102148


Accessories

Optional accessories:


Extension Rod Serie 511

125mm, 9mm Rod Diameter
Art No. 953549
Suggested retail price: 230.00 €*



Extension Rod Serie 511

250mm, 9mm Rod Diameter
Art No. 953550
Suggested retail price: 257.00 €*



Extension Rod Serie 511

500mm, 9mm Rod Diameter
Art No. 953551
Suggested retail price: 399.00 €*


Extension Rod Serie 511

125mm, 12mm Rod Diameter
Art No. 953552
Suggested retail price: 251.00 €*


Extension Rod Serie 511

250mm, 12mm Rod Diameter
Art No. 953553
Suggested retail price: 275.00 €*


Extension Rod Serie 511

500mm, 12mm Rod Diameter

Art No. 953554

Suggested retail price: 493.00 €*


Extension Rod Serie 511

750mm, 12mm Rod Diameter


Art No. 953555

Suggested retail price: 655.00 €*


Extension Rod Serie 511

1000mm, 12mm Rod Diameter

Art No. 953556

Suggested retail price: 907.00 €*


Extension Rod Serie 511

125mm, 15mm Rod Diameter


Art No. 953557

Suggested retail price: 257.00 €*



Extension Rod Serie 511

250mm, 15mm Rod Diameter


Art No. 952361

Suggested retail price: 264.00 €*



Extension Rod Serie 511

500mm, 15mm Rod Diameter
Art No. 953558
Suggested retail price: 622.00 €*



Extension Rod Serie 511

750mm, 15mm Rod Diameter
Art No. 953559
Suggested retail price: 815.00 €*



Extension Rod Serie 511

1000mm, 15mm Rod Diameter
Art No. 953560
Suggested retail price: 1,070.00 €*


Digital Indicator, Bore Gauge ID-C

12,7mm, 0,001mm, Flat Back Plate
Art No. 543-310B-10
Suggested retail price: 563.00 €*


Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application




Dial Gauge, Flat Back, ISO Type

Jewelled Bearing, Shockproof, 1mm, 0,001mm

Art No. 2109AB-10

Suggested retail price: 106.00 €*



Protector for Indicator (plastic cover)

Art No. 21DZA000

Suggested retail price: 20.00 €*




2-Point Inside Measuring Instrument

Bore Gauge, 18-35mm, w/o Indicator

Art No. 511-701

Suggested retail price: 290.00 €*



2-Point Inside Measuring Instrument

Bore Gauge, 35-60mm, w/o Indicator

Art No. 511-702

Suggested retail price: 297.00 €*




2-Point Inside Measuring Instrument

Bore Gauge, 50-150mm, w/o Indicator
Art No. 511-703
Suggested retail price: 310.00 €*



Carbide Tipped Anvil Series 511

Range 18 mm
Art No. 21DZA213A
Suggested retail price: 11.00 €*



Carbide Tipped Anvil Series 511

Range 20 mm
Art No. 21DZA213B
Suggested retail price: 11.00 €*




Carbide Tipped Anvil Series 511

Range 22 mm
Art No. 21DZA213C
Suggested retail price: 11.00 €*




Carbide Tipped Anvil Series 511

Range 24 mm
Art No. 21DZA213D
Suggested retail price: 12.00 €*




Carbide Tipped Anvil Series 511

Range 26 mm
Art No. 21DZA213E
Suggested retail price: 12.00 €*



Carbide Tipped Anvil Series 511

Range 28 mm
Art No. 21DZA213F
Suggested retail price: 12.00 €*



Carbide Tipped Anvil Series 511

Range 30 mm
Art No. 21DZA213G
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 32 mm
Art No. 21DZA213H
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 34 mm
Art No. 21DZA213J
Suggested retail price: 13.00 €*



Washer Series 511

0,5mm, Range 18-35mm
Art No. 205623
Suggested retail price: 7.00 €*



Washer Series 511

1mm, Range 18-35mm
Art No. 205624
Suggested retail price: 7.00 €*



Spanner/526

Art No. 102148
Price on application



Carbide Tipped Anvil Series 511

Range 50mm (100mm)
Art No. 21DZA232A
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 40mm, 55mm (105mm)
Art No. 21DZA232B
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 45mm, 60mm (110mm)
Art No. 21DZA232C
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 50mm, 65mm (115mm)
Art No. 21DZA232D
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 55mm, 70mm (120mm)
Art No. 21DZA232E
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 60mm, 75mm (125mm)
Art No. 21DZA232F
Suggested retail price: 13.00 €*



Carbide Tipped Anvil Series 511

Range 80mm (130mm)
Art No. 21DZA232G
Suggested retail price: 15.00 €*

Carbide Tipped Anvil Series 511



Range 85mm (135mm)
Art No. 21DZA232H
Suggested retail price: 15.00 €*

Carbide Tipped Anvil Series 511



Range 90mm (140mm)
Art No. 21DZA232J
Suggested retail price: 16.00 €*

Carbide Tipped Anvil Series 511



Range 95mm (145mm)
Art No. 21DZA232L
Suggested retail price: 16.00 €*

Carbide Tipped Anvil Series 511



Range 100mm (150mm)
Art No. 21DZA232M
Suggested retail price: 16.00 €*

Washer Series 511



0,5mm, Range 35-160mm
Art No. 205457
Suggested retail price: 7.00 €*



Washer Series 511

1 mm, Range 35-160mm
Art No. 205458
Suggested retail price: 7.00 €*




Washer Series 511

2 mm, Range 35-160mm
Art No. 205459
Suggested retail price: 7.00 €*



Washer Series 511

3 mm, Range 35-160mm
Art No. 205460
Suggested retail price: 7.00 €*



Sub-Anvil Series 511

50 mm
Art No. 102178
Suggested retail price: 24.00 €*