


Digital ABS Caliper with Nib Style Jaws

Item number: 550-227-10

Images




Description

A Mitutoyo waterproof digital caliper suitable for use in the presence of coolant or cutting oil. Hardened stainless steel construction and equipped with special nib-style jaws. ABSOLUTE System scale for error free, high-speed measurement. SPC data output.

Features

Model:	CDC-40"C
Digital/Analog:	Digital
Inch-Metric:	Inch/Metric
Range:	0 - 40 "
Inside measuring from:	1004"/25.5 mm
Delivered:	In a box with SR44 battery
Max. Permissible Error E MPE:	±0.003"
Max. Permissible Error S MPE:	±0.003"
Digital step:	0.0005"/0.01 mm
Max. response speed:	Unlimited
Display:	LCD, character height 9 mm (200 mm) 11 mm (300 mm) 10 mm (>300 mm)
Battery life:	Approx. 5 years, 3,5 years (>300 mm)
ORIGIN (ABS-Zero):	Yes
ON/OFF:	Yes
Low voltage alarm:	Yes
Data output:	Yes
Mass:	3350 g

Dimensions



d: 140 mm

g: 12.7 mm

s: 24 mm

w: 172 mm

h: 32 mm

t: 8 mm

R: 12.7 mm

Accessories

Optional accessories:

Mitutoyo

MiCAT
the standard in world
metrology software
MeasurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Suggested retail price: 340.00 €*

USB-ITPAK

Digimatic Cable, Straight, Data Button,

1m

Art No. 959149

Suggested retail price: 48.00 €*

Digimatic Cable, Straight, Data Button

2m

Art No. 959150

Suggested retail price: 57.00 €*



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Straight,
with Data Button
Art No. 06AFM380C
Suggested retail price: 124.00 €*



U-WAVE-T, Buzzer Type

Wireless Transmitter
Art No. 02AZD880G
Suggested retail price: 187.00 €*



U-WAVE-T, IP67 Type

Wireless Transmitter
Art No. 02AZD730D
Suggested retail price: 163.00 €*



Connection Cable C for U- WAVE

Straight, with Data Button
Art No. 02AZD790C
Suggested retail price: 105.00 €*



Data Hold Unit

for Digital Caliper
Art No. 959143
Suggested retail price: 39.50 €*

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
