

Digital ABS Depth Gauge IP67, Hook Type

Item number: 571-265-20

Images



ABSOLUTE[®]

IP67

Description

Desc

Features

Inch-Metric:	Inch/Metric
Digital/Analog:	Digital
Power supply:	1 battery SR-44
Depth range:	0.404-8.4"
Hook range:	0-8"
Digital step:	0.005"/0.01 mm
ORIGIN (ABS-Zero):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Base (W x T):	3.93" x 0.23"
Max. response speed:	Unlimited
Data output:	Yes
Functions:	Hook Type
Battery life:	Approx. 5 years
Display:	LCD, Character Height 9 mm
Mass:	236 g
Delivered:	In a box with SR44 battery

Accessories

Optional accessories:

Promotion!

Mitutoyo

MiCAT
the standard in world
metrology software
MeasurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Promo price: **268.00 €***

Suggested retail price: ~~340.00 €*~~



Digimatic Cable with Data Button IP Type



1 m, Caliper Type

Art No. 05CZA624

Suggested retail price: 100.00 €*

Digimatic Cable with Data Button IP Type



2 m, Caliper Type

Art No. 05CZA625

Suggested retail price: 107.00 €*

Promotion!

USB Input Tool Direct (Digimatic to USB)



2m Cable, Digimatic/Digimatic 2, with Data Button IP Caliper Type

Art No. 06AFM380A

Promo price: **111.00 €***

Suggested retail price: ~~141.00 €*~~

Promotion!

U-WAVE fit, IP67 Type



Wireless Transmitter for Caliper

Art No. 264-620

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit, Buzzer Type

Wireless Transmitter for Caliper
Art No. 264-621

Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for Caliper
Art No. 264-624

Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for Caliper
Art No. 264-625

Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



Connection Unit for IP Caliper, Micrometer

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth
Art No. 02AZF310

Promo price: **76.00 €***
Suggested retail price: ~~110.00 €*~~

Extension Base, Depth Gauge

180mm width for up to 300mm Range
Art No. 900370
Suggested retail price: 69.00 €*



Extension Base, Depth Gauge

260mm width for up to 300mm Range

Art No. 900371

Suggested retail price: 93.00 €*


Extension Base, Depth Gauge

320mm width for up to 300mm Range

Art No. 900372

Suggested retail price: 107.00 €*


Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
