

Digital ABS AOS Caliper, Inch/Metric

Item number: 573-291-30

Images



ABSOLUTE®

Description

The ABSOLUTE Digimatic calipers have a load cell and help you measure elastic workpieces.

They offer you the following benefits:

- Due to their low and constant measuring force these calipers are ideal for measuring elastic workpieces such as plastic and rubber parts that standard calipers cannot measure accurately.
- Large character height (alleviation of fatigue with the high-contrast LCD)
- The ABS (ABSOLUTE) scale requires no origin setting after power-on and also has no limit to response speed.
- Extraordinary battery life.

Features

Measuring force:	0.5-1 N
Range:	0 - 7 "
Delivered:	In a box with SR44 battery
Max. Permissible Error E MPE:	±0.002"
Digital step:	0.0005"/0.01 mm
Max. response speed:	Unlimited
Jaw retraction:	0.3 mm
Display:	LCD, character height 9 mm
ORIGIN (ABS-Zero):	Yes
ON/OFF:	Yes
ABS / INC (INC ZERO):	Yes

Low voltage alarm:	Yes
Data output:	Yes
Battery life:	Approx. 18000 hours
Mass:	253 g

Accessories

Optional accessories:

Promotion!

Mitutoyo

MiCAT
the standard in world metrology software
MeasurLink



USB-ITPAK Vers. 3.0
USB Dongle + Manual (Software available Online)
Art No. 06AGR543
Promo price: **268.00 €***
~~Suggested retail price: 340.00 €*~~



Digimatic Cable, Straight, Data Button,

1 m
Art No. 959149
Suggested retail price: 48.00 €*



Digimatic Cable, Straight, Data Button

2 m
Art No. 959150
Suggested retail price: 57.00 €*

Promotion!



USB Input Tool Direct (Digimatic to USB)
2m Cable, Digimatic/Digimatic 2, Straight, with Data Button
Art No. 06AFM380C
Promo price: **98.00 €***
~~Suggested retail price: 124.00 €*~~

Promotion!



U-WAVE fit, IP67 Type

Wireless Transmitter for Caliper
Art No. 264-620

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit, Buzzer Type

Wireless Transmitter for Caliper
Art No. 264-621

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for Caliper
Art No. 264-624

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for Caliper
Art No. 264-625

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



Connection Unit for Standard Caliper

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth

Art No. 02AZF300

Promo price: **72.00 €***

Suggested retail price: ~~105.00 €*~~




Data Hold Unit

for Digital Caliper
Art No. 959143
Suggested retail price: 39.50 €*



Depth Base Attachment for Caliper

75mm width for 100, 150, 200mm Range
Art No. 050083-10
Suggested retail price: 60.00 €*



Depth Base Attachment for Caliper

100mm width for 100, 150, 200mm Range
Art No. 050084-10
Suggested retail price: 67.00 €*

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882
Suggested retail price: 7.00 €*