


## Digital ABS Point Caliper (Point Type)

Item number: 573-625-20

### Images



Dust- and  
Water-  
Protected

www.tuv.com  
ID 0000045042

# ABSOLUTE®

# IP67

### Description



Pointed caliper with depth gauge

### Features

<b>Delivered:</b>	In a box with SR44 battery
<b>Range:</b>	0 - 150 mm
<b>Thumb roller:</b>	Yes
<b>Max. Permissible Error E MPE:</b>	±0,02 mm
<b>Max. Permissible Error S MPE:</b>	±0,04 mm
<b>Max. response speed:</b>	Unlimited
<b>ORIGIN (ABS-Zero):</b>	Yes
<b>Auto Power OFF after 20 min. non use:</b>	Yes

<b>Low voltage alarm:</b>	Yes
<b>Data output:</b>	Yes
<b>Functions:</b>	Pointed measuring jaws
<b>Battery life:</b>	Approx. 5 years under normal use
<b>Mass:</b>	163 g

## Dimensions



## Accessories

### Optional accessories:

Promotion!

Mitutoyo

MiCAT

the standard in world  
metrology software  
MeasurLink®

### USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Promo price: **259.00 €\***

Suggested retail price: ~~340.00 €\*~~

USB-ITPAK

### Digimatic Cable with Data Button IP Type

1m, Caliper Type

Art No. 05CZA624

Suggested retail price: 100.00 €\*





### Digimatic Cable with Data Button IP Type

2m, Caliper Type  
Art No. 05CZA625  
Suggested retail price: 107.00 €\*  
\*including VAT

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Caliper Type  
Art No. 06AFM380A  
Promo price: **109.00 €\*  
Suggested retail price: 141.00 €\*  
\*including VAT**

Promotion!



### U-WAVE fit, IP67 Type

Wireless Transmitter for Caliper  
Art No. 264-620  
Promo price: **129.00 €\*  
Suggested retail price: 185.00 €\*  
\*including VAT**

Promotion!



### U-WAVE fit, Buzzer Type

Wireless Transmitter for Caliper  
Art No. 264-621  
Promo price: **129.00 €\*  
Suggested retail price: 185.00 €\*  
\*including VAT**

Promotion!



### U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for Caliper  
Art No. 264-624  
Promo price: **139.00 €\*  
Suggested retail price: 185.00 €\*  
\*including VAT**

Promotion!



### U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for Caliper  
Art No. 264-625

Promo price: **139.00 €\***  
Suggested retail price: ~~185.00 €\*~~

Promotion!



### Connection Unit for IP Caliper, Micrometer

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth

Art No. 02AZF310

Promo price: **74.90 €\***  
Suggested retail price: ~~110.00 €\*~~


#### Standard accessories:



### Depth Base Attachment for Caliper

75mm width for 100, 150, 200mm Range  
Art No. 050083-10

Suggested retail price: **60.00 €\***



### Depth Base Attachment for Caliper

100mm width for 100, 150, 200mm Range  
Art No. 050084-10

Suggested retail price: **67.00 €\***

#### Spare parts

#### Consumable spares:



## Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 10.00 €\*  

---