

Digital ABS Offset Caliper, IP67

Item number: 573-701-20

Images



Dust- and
Water-
Protected

www.tuv.com
ID 0000045042

ABSOLUTE®

IP67

Description


A Mitutoyo waterproof digital caliper suitable for use in the presence of coolant or cutting oil. Equipped with special offset-style jaws. ABSOLUTE System scale for error free, high-speed measurement. SPC data output.

Features

Range:	0 - 6 "
Delivered:	In a box with SR44 battery
Max. Permissible Error E MPE:	±0.001"
Max. Permissible Error S MPE:	±0.002"
Digital step:	0.0005"/0.01 mm
Max. response speed:	Unlimited
Display:	LCD, character height 9 mm (150, 200 mm) 11 mm (300 mm)
ORIGIN (ABS-Zero):	Yes

Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Data output:	Yes
Battery life:	Approx. 5 years under normal use
Mass:	168 g

Dimensions



a: 95 mm

b: 10 mm

c: 40 mm

d: 30 mm

Accessories

Optional accessories:

Promotion!

Mitutoyo

MICAT
the standard in world metrology software
measurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Promo price: 268.00 €*

~~Suggested retail price: 340.00 €*~~





Digimatic Cable with Data Button IP Type

1 m, Caliper Type
Art No. 05CZA624
Suggested retail price: 100.00 €*



Digimatic Cable with Data Button IP Type

2 m, Caliper Type
Art No. 05CZA625
Suggested retail price: 107.00 €*

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data
Button IP Caliper Type
Art No. 06AFM380A

Promo price: **111.00 €***

Suggested retail price: ~~141.00 €*~~

Promotion!



U-WAVE fit, IP67 Type

Wireless Transmitter for Caliper
Art No. 264-620

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit, Buzzer Type

Wireless Transmitter for Caliper
Art No. 264-621

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for Caliper
Art No. 264-624

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for Caliper
Art No. 264-625

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



Connection Unit for IP Caliper, Micrometer

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth

Art No. 02AZF310

Promo price: **76.00 €***

Suggested retail price: ~~110.00 €*~~



Depth Base Attachment for Caliper

75mm width for 100, 150, 200mm Range

Art No. 050083-10

Suggested retail price: **60.00 €***



Depth Base Attachment for Caliper

100mm width for 100, 150, 200mm Range

Art No. 050084-10

Suggested retail price: **67.00 €***

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: **7.00 €***